

W74D

Excelon® 74 Desiccant
Compressed Air Dryer
3/8", and 1/2" Port Sizes

Helps eliminate condensate at point-of-use.

**Typical dew point suppression of 15°F (-10°C)
below inlet ambient pressure dew point.**

**Membrane Dryers**

W07M, W72M, and W74M Series
Membrane Dryer
1/4", and 1/2" Port Size

**Removes water vapor from compressed air providing
condensate-free air at the point of application.**

**Provides dewpoint suppression up to 80°F (44°C)
depending on air flow through the membrane**

**Dewpoint suppression of 20°F (11°C)
below the inlet temperature is suitable
for most industrial applications.**

**Utilizes the latest membrane technology to
achieve optimal water vapor removal rates.**

