



valve operation codes.
+++++

code;	operation;
++++	++++++
I	push button, spring return
2	pressure operated, air return
3	pressure operated, pressure return
6	lever operated, spring return
7	2 or 3 position lever operated, lever return
8	roller operated, spring return
9	Foot operated, spring return
I0	foot operated (treadle)
I1	lever bleed operated, auto return
I3	push pull operated
I4	plunger operated, spring return
I7	pedal operated, air reset
22	solenoid operated, spring return, external pilot
23	solenoid operated, solenoid return, external pilot
29	push button operated, pull or air reset
30	push button set, pressure reset
33	pressure priority set, pressure reset
34	roller operated, air return
37	solenoid operated, air return, external pilot supply
40	pressure operated, spring return
41	plunger bleed operated, auto return
42	diaphragm operated, spring return
45	pressure operated, spring & air return
48	one way trip operated, spring return
49	key operated set & reset
51	shrouded button operated, spring return, panel mtd.
63	double pressure operated, spring to mid position
72	solenoid operated, spring & air return, external pilot
83	palm button operated, spring return
87	2 or 3 position lever operated, lever return
I07	rotary lever set & reset
I09	pedal operated, spring & air return
I17	long lever set & reset
I22	solenoid operated, spring reset
I23	solenoid operated, solenoid reset
I52	solenoid operated, spring & air reset
I72	single solenoid operated, spring & air reset
307	rotary knob set & reset
348	one way trip operated, air reset
623	double solenoid operated, spring to mid position
687	lever operated, spring to mid position
6I23	double solenoid operated, integral pilot, air/spring to mid position

air return; compressed
air
pressure operated; air signal
bleed; constant air
flow..