

- Impermeable to gasses and moisture
- Lightweight, flexible, and excellent for food and beverage applications
- > Low Density Polyethylene (LDPE)
- > Tasteless and odorless
- > Easily heat sealed
- > All colors except red, comply with FDA Regulation 21 CFR 177.1520(c) for food contact applications



Technical data Medium:

Compressed air, water, steam, and other non-flammable, inert gases and liquids

Temperature range: -40° to 150°F (-40° to 66°C) **Vacuum rating:** To 28" Hg **Diameter tolerance:** ± .004 **Hardness:** LDPE: 44 Shore D Tube markings: FW specifications Base resin compliance: FDA (except red) Recommended fittings Push-in, compression

| Part Number 100' length | Color | Size tube 0.D. (inch) | Size tube I.D. (inch) | Wall thickness (inch) | Workin @75F / 25°C | g pressure PSI @150°F / 65°C | Weight Ibs./100' | Bend radius |
|----------------------------|---------|--------------------------|--------------------------|--------------------------|-----------------------|---------------------------------|---------------------|----------------|
| \bigcirc | | | | | | | | |
| PE0051100 | natural | 1/8 | 0.62 | 0.031 | 305 | 120 | .40 | 1/2" |
| PE0052100 | natural | 5/32 | .106 | 0.025 | 175 | 70 | .46 | 1" |
| PE0054100 | natural | 1/4 | .170 | 0.040 | 200 | 80 | 1.2 | 1-1/4" |
| PE0056100 | natural | 3/8 | .250 | 0.062 | 190 | 75 | 2.76 | 2" |
| PE0057100 | natural | 1/2 | .375 | 0.062 | 135 | 55 | 3.87 | 2-1/2" |

| Part Number 100' length | Color | Size tube 0.D. (inch) | Size tube I.D. (inch) | Wall thickness (inch) | Workin @75F / 25°C | g pressure PSI @150°F / 65°C | Weight Ibs./100' | Bend radius |
|----------------------------|-------|--------------------------|--------------------------|--------------------------|-----------------------|---------------------------------|---------------------|----------------|
| 0 | | | | | | | | |
| PE0151100 | red | 1/8 | 0.62 | 0.031 | 305 | 120 | .40 | 1/2" |
| PE0152100 | red | 5/32 | .106 | 0.025 | 175 | 70 | .46 | 1" |
| PE0154100 | red | 1/4 | .170 | 0.040 | 200 | 80 | 1.2 | 1-1/4" |
| PE0156100 | red | 3/8 | .250 | 0.062 | 190 | 75 | 2.76 | 2" |
| PE0157100 | red | 1/2 | .375 | 0.062 | 135 | 55 | 3.87 | 2-1/2" |

| Part Number 100' length | Color | Size tube O.D. (inch) | Size tube I.D. (inch) | Wall thickness (inch) | Workin @75F / 25°C | g pressure PSI @150°F / 65°C | Weight Ibs./100' | Bend radius |
|----------------------------|-------|--------------------------|--------------------------|--------------------------|-----------------------|---------------------------------|---------------------|----------------|
| 0 | | | | | | | | |
| PE0751100 | black | 1/8 | 0.62 | 0.031 | 305 | 120 | .40 | 1/2" |
| PE0752100 | black | 5/32 | .106 | 0.025 | 175 | 70 | .46 | 1" |
| PE0754100 | black | 1/4 | .170 | 0.040 | 200 | 80 | 1.2 | 1-1/4" |
| PE0756100 | black | 3/8 | .250 | 0.062 | 190 | 75 | 2.76 | 2" |
| PE0757100 | black | 1/2 | .375 | 0.062 | 135 | 55 | 3.87 | 2-1/2" |

Warning

Improper selection, misuse, age or malfunction of components used in systems can cause failure in various modes. The system designer is warned to consider the failure modes of all component parts and to provide adequate safeguards to prevent personal injury or damage to equipment or property in the event of such failure modes. System designers and end users are cautioned to consult instruction sheets and specifications available from the factory. The system designer/end user is responsible for verifying that all requirements for the application are met.

Warranty

The products described herein are warranted subject to seller's Standard Terms and Condition of Sale, available at seller's website.

Proposition 65: These products may contain chemicals known to the state of California to cause cancer, or birth defects, or other reproductive harm.



Our policy is one of continued research and development. We therefore reserve the right to amend, without notice, the specifications given in this document. © 2016 Norgren, Inc.