



NVP Series Venturi Vacuum Pump

Installation & Maintenance Instructions

Engineering
GREAT
Solutions



Installation Instructions

1. Mount pump to your mounting hardware, end-of-arm-tool, extrusion, etc. NVP00 and NVP10 model pumps have two mounting holes that accept 4-40 (M3) screws. NVP20, VP80, and NVP90 pumps have three mounting holes that accept 10-32 (M5) screws (screws not supplied). Pumps work in any orientation.
2. Attach air line to air supply port. Attach vacuum line to vacuum port if not directly attaching a vacuum cup to the port. See chart on page 2 for minimum recommended sizes (tubing outer diameters are listed).
3. Turn on compressed air and regulate to specified pressure (80 PSI standard, models with “-60” designation to 60 PSI – set regulator while pump is operating). The NVP pump will generate vacuum immediately.

NVP Series Model	Air Supply Port Threads	Recommended Air Supply Line (outer diameter)	Vacuum Port Threads	Recommended Vacuum Line (outer diameter)
NVP00-60 (M,H) Series	10-32 UNC Female	1/4" [6 mm]	10-32 UNC Female	1/4" [6 mm]
NVP10-(60,90) (L,M,H) Series	1/4 NPT	1/4" [6 mm]	1/8 NPT	1/4" [6 mm]
NVP10-(100,150) (L,M,H) Series	1/4 NPT	3/8" [10 mm]	1/8 NPT	3/8" [10 mm]
NVP20-(60,90) (L,M,H) Series	1/4 NPT	1/4" [6 mm]	1/4 NPT	1/4" [6 mm]
NVP20-(100,150) (L,M,H) Series	1/4 NPT	3/8" [10 mm]	1/4 NPT	3/8" [10 mm]
NVP80-200 (L,M,H) Series	1/4 NPT	3/8" [10 mm]	3/8 NPT	3/8" [10 mm]
NVP80-250 (L,M,H) Series	1/4 NPT	3/8" [10 mm]	3/8 NPT	1/2" [12 mm]
NVP90-300 (L,M,H) Series	3/8 NPT	1/2" [12 mm]	1/2 NPT	1/2" [12 mm]
NVP90-350 (L,M,H) Series	3/8 NPT	1/2" [12 mm]	1/2 NPT	1/2" [12 mm]

The recommended tubing sizes are based on polyethylene or polyurethane tubing with 0.062" [1/16", 1.5 mm] wall thickness
 Note: IMI Norgren discourages the use of quick disconnect fittings on all connections

Norgren Inc.
5400 South Delaware Street, Littleton, CO 80120 USA
Tel: +1 (800) 514 0129
Sales.usa@imi-precision.com
www.imi-precision.com

Warning

These products are intended for use in industrial systems only. Do not use these products where pressures and temperatures can exceed those listed under Specifications.

Before using these products with fluids other than those specified, for nonindustrial applications, life-support systems, or other applications not within published specifications, consult Norgren.

Through misuse, age, or malfunction, components used in fluid power systems can fail in various modes. The system designer is warned to consider the failure modes of all component parts used in fluid power systems and to provide adequate safeguards to prevent personal injury or damage to equipment in the event of such failure modes.

System designers must provide a warning to end users in the system instructional manual if protection against a failure mode cannot be adequately provided. System designers and end users are cautioned to review specific warnings found in instruction sheets packed and shipped with these products. System designers should also provide for all OSHA requirements including Title 29 CFR 1910.147 Lockout/Tagout.

It should be recognized that warnings are valid for any product, regardless of manufacturer, and are not restricted to products manufactured by Norgren. Norgren's reputation for product quality and performance is well established. We feel we have the additional obligation to provide information or warnings to customers to assist them in applying our products in a reasonable and safe manner.

Warranty

Items sold by Norgren are warranted to be free from defects in materials and workmanship for a period of two year from the date of manufacture, provided said items are used according to Norgren's recommended usages. Norgren's liability is limited to the repair of, refund of purchase price paid for, or replacement in kind of, at Norgren's sole option, any items proved defective, provided the allegedly defective items are returned to Norgren prepaid. The warranties expressed above are in lieu of and exclusive of all other warranties. There are no other warranties, expressed or implied, except as stated herein.

 **WARNING:** Cancer and Reproductive Harm - www.p65warnings.ca.gov.

Our policy is one of continued research and development. We therefore reserve the right to amend, without notice, the specifications given in this document.

© Norgren, Inc. 2019