

True modularity with Norgren Quikclamp® connections

Quick release bayonet bowl

Lubricator flow sensor provides a nearly constant oil/air ratio over a wide range of air flows

All around (360°) visibility of the lubricator sight-feed dome simplifies installation and adjustment

Regulator balanced valve minimizes effect of variation in the inlet pressure on the outlet pressure



Technical data

Refer to individual component sections for product specifications

Ordering information


Models listed include PTF threads. Filter (F) includes automatic drain, metal bowl with level indicator, and a 40µm element. Regulator (R) is relieving type with knob adjustment, 150 psig (10 bar) regulating spring, and gauge. Lubricator (L) is a Micro-Fog model with 1/4 turn manual drain and metal bowl with level indicator.

Combination Unit Type	Port Size	Model**	Weight lb (kg)
Filter-Regulator-Lubricator	1/4"	C72H-2AK-AE3-RMG-QEB	2.37 (1.08)
	3/8"	C73H-3AK-AD3-RMG-QDB	3.0 (1.36)
	1/2"	C74H-4AK-AD3-RMG-QDB	5.07 (2.30)
	3/4"	C74H-6AK-AD3-RMG-QDB	5.0 (2.27)


** For oil fog lubricator use "B" in the 4th position.

Other combinations are available. Please consult Technical support for more information.


C72H-



C73H-



C74H-



Dimensions in inches (mm).