

Non-relieving models for air and water service
Relieving models for air service allow reduction of outlet pressure even when the system is dead-ended
R14 has aluminum body and bonnet
R16 has brass body and bonnet
Factory preset, tamper resistant pressure setting


R14

R16

Technical data
Technical data
Fluid:

R14: Compressed air, neutral gases

NOTE: Contact technical support for use with other media.

R16: Water and compressed air

Maximum inlet pressure:
 400 psig (27 bar)

Operating temperature

Water service: 35° to 175°F (2° to 79°C)†

Air service: -30° to 175°F (-34° to 79°C)*

* Air supply must be dry enough to avoid ice formation at temperatures below 35°F (2°C).

† R16 brass bonnet & body combination max temp. 200°F.

Type

R14: Piston, relieving or non-relieving

R16: Diaphragm, relieving or non-relieving

Gauge ports:

1/8" PTF

Factory preset outlet pressure settings:

3 to 99 psig (0.2 to 6.8 bar)

Outlet pressure tolerance:

 Outlet pressure setting - psig (bar)
 Tolerance - psig (bar)**

 3 to 20 psig (0.21 to 1.38 bar) ± 1.0 psig (0.07 bar)
 21 to 50 psig (1.45 to 3.45 bar) ± 2.0 psig (0.14 bar)

51 to 99 psig (3.52 to 6.84 bar) ± 3.0 psig (0.21 bar)

** When outlet pressure is preset at the factory, the following conditions exist

Inlet pressure:

100 psig (6.9 bar) for outlet pressures up through 95 psig (6.6 bar)

125 psig (8.6 bar) for outlet pressures of 96 through 99 psig (6.7 through 6.8 bar)

Materials

Body and bonnet

R14: aluminum

R16: brass


Valve: brass, nitrile

Valve seat: acetal resin

Elastomers: nitrile

Ordering information

Models listed are relieving type for compressed air service with PTF threads and with gauge ports.

ISO Symbols	Port	Model	Flow† scfm (dm3/s)	Flow†† U.S. gpm (lpm)	Weight lb (kg)
	1/8" PTF	R14-100-R**A	12 (5.7)	1.3 (4.9)	0.2 (0.09)
	1/8" PTF	R16-100-R**A	12 (5.7)	1.3 (4.9)	0.7 (0.32)
	1/4" PTF	R14-200-R**A	12 (5.7)	1.3 (4.9)	0.2 (0.09)
	1/4" PTF	R16-200-R**A	12 (5.7)	1.3 (4.9)	0.7 (0.32)

† Approximate flow with 100 psig (7 bar) inlet pressure, 80 psig (5.5 bar) set pressure and a 15 psig (1 bar) droop from set.

†† Approximate flow with 100 psig (7 bar) inlet pressure, 60 psig (4 bar) set pressure and a 15 psig (1 bar) droop from set.

Alternative Models

Type/Service	Substitute
Piston; air service only	14
Diaphragm; air and water service	16
Port Size	Substitute
1/8"	1
1/4"	2
Gauge ports in body	Substitute
With gauge ports	00
Without gauge ports	01
Diaphragm	Substitute
Relieving	R
Non relieving	N




R ★ ★ - ★ ★ ★ - ★ ★ ★ ★

Threads	Substitute
PTF	A

** The 8th and 9th positions of the model number contain the Modified Outlet Pressure Setting. The Modified Outlet Pressure Setting is the desired outlet pressure, modified to allow for inlet pressures other than 100 psig, and for flows other than zero. Insert the modified outlet pressure setting in positions 8 and 9 as described below.

1. Write down the desired outlet pressure and the flow through the regulator. EXAMPLE: 30 psig outlet pressure at 10 scfm flow.
 2. Modifications for inlet pressures other than 100 psig: If inlet pressure exceeds 100 psig*, add 1 psig to the desired outlet pressure for each 20 psig the inlet pressure is above 100 psig*. EXAMPLE: If the inlet pressure is 180 psig, add 4 to the desired outlet pressure. Following through with the example in step 1, add 4 to 30 for a modified outlet pressure setting of 34 psig. If inlet pressure is less than 100 psig*, subtract 1 psig from the desired outlet pressure for each 20 psig the inlet pressure is below 100 psig*. EXAMPLE: If the inlet pressure is 60 psig, subtract 2 from the desired outlet pressure. Following through with the example in step 1, subtract 2 from 30 for a modified outlet pressure setting of 28 psig.
 3. Modifications for flows other than zero: Determine the pressure drop from the appropriate flow curve above. Add the pressure drop to the modified outlet pressure setting. EXAMPLE: If the desired outlet pressure is 30 psig at a flow of 10 scfm, add 10 to the modified outlet pressure setting. The quantity of 10 is the difference between the outlet pressure (30 psig) at the desired flow (10 scfm) and outlet pressure (40 psig) at no flow. See dashed lines on the air flow curve for example. Following through with the first example in Step 2 above, add 10 to the 34 to obtain a modified outlet pressure setting of 44. Enter 44 in the 8th and 9th positions of the model number.
- * 125 psig for outlet pressure settings of 95 through 99 psig.

Typical Performance Characteristics



Dimensions in inches (mm)