


- > Port size: 1/8" & 1/4" (ISO G/NPT)
- > Enables air to be exhausted quickly from air cylinders
- > Allows higher cylinder speeds to be achieved
- > Simple, compact design and construction
- > Very reliable in operation
- > Wide temperature range
- > Shock and vibration resistant to EN 61373, Category 1, class A and B



**Technical features**

**Medium:**  
Compressed air, filtered, lubricated or non-lubricated

**Operation:**  
Poppet valve

**Operating pressure:**  
0,5 ... 10 bar (7 ... 145 psi)

**Port size:**  
G1/8, G1/4, 1/8 NPT, 1/4 NPT

**Mounting:**  
Line mounted

**Ambient/Media temperature:**  
-40°C ... +80°C max.  
( -40 ... +176°F)  
Air supply must be dry enough to avoid ice formation at temperatures below +2°C (+35°F)

**Materials:**  
Body and Cover:  
Aluminium or zinc alloy  
Seals: NBR

**Technical data, standard models**

Symbol	Port size			Flow factor 1 » 2		2 » 3 Cv	Kv *2)	Flow from at 6 » 5 bar (m³ / h)		Weight (kg)	Spare kit	Model
	Inlet	Outlet	Exhaust	Cv	Kv *2)			1 » 2	2 » 3			
	G1/8	G1/8	G1/8	0,9	1,06	1,8	1,23	95,8	110,9	0,15	LT70C1800K0	LT70C1800
	1/8 NPT	G1/8	G1/8	0,9	1,06	1,8	1,23	95,8	110,9	0,15	LT70C1800K0	LT70A1800
	G1/4	G1/4	G1/4	1,9	2,23	2,5	2,46	201,6	221,8	0,13	LT70C2800K0	LT70C2800
	1/4 NPT	G1/4	G1/4	1,9	2,23	2,5	2,46	201,6	221,8	0,13	LT70C2800K0	LT70A2800

\*1) Measured in dm³/(s.bar)  
\*2) Measured in m³/h


**Options selector**

LT70★★★00


Thread form	Substitute	Port size	Substitute
ISO G, parallel	C	1/8"	18
NPT	A	1/4"	28

**Characteristic curves**

Choked flow versus inlet pressure  
Way (1 » 2) and (2 » 3)





**Drawing**



Dimensions in mm  
Projection/First angle



A	ØB	D	F	G	H	ØJ	K		 1	Model
1/8"	19	28	15,5	3,5	53	29	35,5	19	30	LT70#1800
1/4"	19	28	15,5	3,5	53	29	35,5	19	30	LT70#2800

# Please insert 'C' for ISO G and 'A' for NPT thread

**Warning**

These products are intended for use in industrial compressed air and rail transport systems only. Do not use these products where pressures and temperatures can exceed those listed under

**»Technical features/data«.**

Before using these products with fluids other than those specified, for non-industrial applications, life-support systems or other applications not within published specifications, consult IMI NORGREN.

Through misuse, age, or malfunction, components used in fluid power systems can fail in various modes.

The system designer is warned to consider the failure modes of all component parts used in fluid power systems and to provide adequate safeguards to prevent personal injury or damage to equipment in the event of such failure.

System designers must provide a warning to end users in the system instructional manual if protection against a failure mode cannot be adequately provided.

System designers and end users are cautioned to review specific warnings found in instruction sheets packed and shipped with these products.