

- > Port size: 1/4" (ISO G/NPT)
- > Compact size/low weight/ in-line units
- > High flow performance
- > Suitable for panel and wall mounting*
- > Adjustment can be locked

* Note: In areas of vibration use of panel mounting is not recommended

Technical features

Medium:

Compressed air, filtered, lubricated or non-lubricated, inert gases

Operation: Flow regulators (uni-directional) Captive regulator needle will not blow out when unscrewed

> Wide temperature range

Operating pressure:

Port size:

G1/4, 1/4 NPT

1 ... 10 bar (14 ... 145 psi)

 Shock and vibration resistant to EN 61373, Category 1, class A and B





Ambient/Media temperature:

-40 ... +80°C max. (-40 ... +176°F max.) Air supply must be dry enough to avoid ice formation at temperatures below +2°C (+35°F). Materials: Body: Aluminium alloy (painted) Seals: low NBR Internal parts: Brass External parts: Aluminium alloy (anodised) Needle: Brass (nickel plated)

Technical data, standard models

Symbol	Port size	Max. regulated flow factor C *1) Cv Kv *2)		Free flow factor C *1) Cv Kv *2)			Opening pressure (bar)	Weight (kg)	Model	
	G1/4	1,30	0,32	0,28	2,80	0,69	0,6	< 0,1	0,056	LT1000C2800
1-2	1/4 NPT	1,30	0,32	0,28	2,80	0,69	0,6	< 0,1	0,056	LT1000A2800
لا										

*1) Measured in dm3/(s.bar)

*2) Measured in m³/h

Flow vs turns at 6 bar – flow in dm³/s ANR 1/4" version





Dimensions







G

Please insert 'C' for ISO G and 'A' for NPT thread

Warning

These products are intended for use in industrial compressed air and rail transport systems only. Do not use these products where pressures and temperatures can exceed those listed under **»Technical features/data**«. Before using these products with fluids other than those specified, for non-industrial applications, life-support systems or other applications not within published specifications, consult IMI Precision Engineering, Norgren Ltd.

Through misuse, age, or malfunction, components used in fluid power systems can fail in various modes. The system designer is warned to consider the failure modes of all component parts used in fluid power systems and to provide adequate safeguards to prevent personal injury or damage to equipment in the event of such failure.

System designers must provide a warning to end users in the system instructional manual if protection against a failure mode cannot be adequately provided.

System designers and end users are cautioned to review specific warnings found in instruction sheets packed and shipped with these products.