

Olympian Plus plug in design

Attaches to yoke, upstream or downstream of air processing units.

T64E 3-port/2-position lockout valves help conform to OSHA Lockout Regulations in USA market.†


Technical data
Fluid:

Compressed air, neutral gases

NOTE: Contact technical support for use with other media.

Maximum pressure:

250 psig (17 bar)

Operating temperature*:

0° to 175°F (-20° to 80°C)

* Air supply must be dry enough to avoid ice formation at temperatures below 35°F (2°C).

Cv factor from IN to OUT ports

1/4 port size: 2.6

3/8 port size: 5.5

1/2 port size: 6.7

3/4 port size: 7.5

Exhaust port threads on
T64T models:

1/8 PTF with PTF main ports,

1/8 ISO Rc with ISO G

Materials



Body: zinc

Slide: acetal plastic

Elastomers: nitrile

Ordering information


Models listed include PTF threads in the pilot and exhaust ports.

ISO Symbols	Port Size	Weight lbs (kg)
 2-Port/2-Position	1/4"	0.89 (0.40)
	3/8"	0.88 (0.40)
 3-Port/2-Position	1/2"	0.84 (0.38)
	3/4"	0.84 (0.38)

Service kits*

Type	Part Number
T64E (yellow slide)	4384-211 (OSHA)†
T64T (red slide)	4384-210

Service kit includes seals and slide.



** Models with 3/4" ports

Dimensions in inches (mm)

Options selector

T64★-★★★-P1N

Valve Type	Substitute	Porting	Substitute
3-port/2-position Yellow actuator	E	Threaded inlet only	B
3-port/2-position Red actuator	T	Threaded outlet only	C
Port size	Substitute	Threads	Substitute
1/4"	2	PTF	A
3/8"	3	ISO G parallel	G
1/2"	4		
3/4"	6		