



Option selector B68* - *** Bowl/ Gauge Element With Long Without Port Adjustment Diaphragm G Short Bowl 3/4 Relieving Knob 1 litre (1 quart U.S.) С 8 T-bar Ν Non relieving Thread No liquid indicator 1-1/4 Element Drain PTF 0,5 litre (1 pint U.S.) В 1-1/2 5 µm Automatic Spring (Outlet pressure range) * В ISO Rc tapered No liquid indicator Ν No yoke 25 µm F Closed bottom 0,3 ... 4 bar (5 ... 60 psig) 0,5 litre (1 pint U.S.) G ISO G parallel 40 µm Manual, spindle type Manual, 1/4 turn 0,4 ... 8 bar (5 ... 120 psig) 0,7 ... 17 bar (10 ... 250 psig) Μ Ν No yoke (N in 5th position) Rc gauge ports. With liquid indicator No yoke (N in 5th position) PTF gauge ports 1 litre (1 quart U.S.) * Outlet pressure can be adjusted to pressures in excess of, and less than, those specified. With liquid indicator Do not use these units to control pressures outside of the specified ranges. *1) Available only with T-bar adjustment. **TECHNICAL FEATURES** Filter element, 1 litre bowl, 40 µm (55) 5311-03 Fluid: Compressed air Maximum pressure: Automatic drain, G1/8 outlet (49) 3000-97 17 bar (250 psig) Automatic drain, 1/8 PTF outlet (49) 3000-10 Operating temperature*: Manual drain, spindle type (44) 684-84 -20° ... +80°C (0° ... +175°F) Manual drain, 1/4 turn (40) 619-50 63 * Air supply must be dry enough to avoid ice 4355-51 Tamper resistant cover and wire 62 64) (61)

formation at temperatures below +2°C (+35°F). Particle removal: 5 µm, 25 µm or 40 µm filter element Air quality: Within ISO 8573-1, Class 3 and Class 5 (particulates) Typical flow at 10 bar (150 psig) inlet pressure, 6,3 bar (90 psig) set pressure and a droop of 1 bar (15

psig) from set: 240 dm3/s (509 scfm) 1/4 turn manual drain connection: 1/8" pipe thread

Automatic drain connection: 1/8" pipe thread Automatic drain operating conditions:

Bowl pressure required to close drain:

Greater than 0,3 bar (5 psig)

Bowl pressure required to open drain:

Less than 0,2 bar (3 psig)

Minimum air flow required to close drain:

1 dm3/s (2 scfm)

Manual operation: Depress pin inside drain outlet to drain bowl

Nominal bowl size:

0,5 litre (1 pint U.S.), 1 litre (1 quart U.S.)

Gauge ports:

1/8 PTF with PTF yoke ports

Rc1/8 with ISO Rc yoke ports

Rc1/8 with ISO G yoke ports

Materials:

Body: Aluminium

Yoke: Aluminium

Bonnet: Aluminium

Adjusting knob: Acetal resin

Optional T-bar adjusting screw: Steel

Valve: Aluminium

Bowl: Aluminium

Sight glass: Pyrex

Element: Sintered bronze or polypropylene

Elastomers: Synthetic rubber


REPLACEMENT ITEMS	
Service kit (items circled on exploded view)	
Relieving	4383-300
Nonrelieving	4383-301
0.5 litre bowl liquid level lens	
(19 thru 27)	4380-060
1 litre bowl liquid level lens	
(30 thru 38)	4380-061
Filter element, 0.5 litre bowl, 5 µm	
(54, 55, 56)	5576-97
Filter element, 0.5 litre bowl, 25 µm	
(54, 55, 56)	5576-98
Filter element, 0.5 litre bowl, 40 µm	
(54, 55, 56)	5576-99
Filter element, 1 litre bowl, 5 µm (55)	5311-01
Filter element, 1 litre bowl, 25 µm (55)	5311-02

INSTALLATION


- 1. Install unit vertically in air line -
- · with air flow in direction of arrow on top of yoke,
- · upstream of lubricators and cycling valves,
- · as close as possible to the device being serviced.
- 2. Connect piping to yoke ports using pipe thread sealant on male threads only.
- 3. Install a pressure gauge in regulator or plug gauge ports. Gauge ports can also be used as additional outlets for regulated air.
- 4. Lubricate o-rings (15) with a light coat of o-ring grease, then place o-rings in grooves in body (14).
- 5. Place clamp ring under lugs on top of yoke.
- 6. Make sure arrows on yoke and regulator point in same direction, then plug regulator into yoke and tighten clamp ring hand tight.
- 7. Turn bowl into body until arrowhead on bowl is aligned with or to the right of the arrowhead on the body.
- 8. Flexible tube with 3mm (0.125") minimum I.D. can be connected to the automatic drain. Avoid restrictions in the tube.

ADJUSTMENT

- 1. Before applying inlet pressure to filter/regulator, turn adjustment (1 or 7) counterclockwise to remove all force on regulating spring (11).
- 2. Apply inlet pressure, then turn adjustment (1 or 7) clockwise to increase and counterclockwise to decrease pressure setting.
- 3. Always approach the desired pressure from a lower pressure. When reducing from a higher to a lower setting, first reduce to some pressure less than that desired, then bring up to the desired pressure.



(56)





B68G, B68E Filter/Regulator Installation & Maintenance Instructions



NOTE

With non-relieving filter/regulators, make pressure reductions with some air flow in the system. If made under no flow (dead-end) conditions, the filter/regulator will trap the over-pressure in the downstream line.

- 4. Knob Adjustment. Push knob toward body to lock pressure setting. Pull knob away from body to release. Install tamper resistant cover and wire (see Replacement Items) to make setting tamper resistant.
- 5. T-bar Adjustment. Tighten lock nut (8) lock pressure setting.

SERVICING

- 1. Open manual drain to expel accumulated liquids. Keep liquids below baffle (53).
- 2. Clean or replace filter element when dirty.

DIASSEMBLY

- 1. Shut off inlet pressure. Reduce pressure in inlet and outlet lines to zero.
- 2. Turn adjustment (1 or 7) fully counterclock wise.
- 3. Unscrew clamp ring and remove unit from yoke.
- Disassemble in general accordance with the item numbers on exploded view. Do not remove the drains unless replacement is necessary. Remove and replace only if they malfunction.

CLEANING

- 1. Clean parts with warm water and soap.
- Rinse and dry parts. Blow out internal passages in body with clean, dry compressed air. Blow air through filter element (55) from inside to outside to remove surface contaminants.
- 3. Inspect parts. Replace those found to be damaged.

ASSEMBLY

- Lubricate o-rings, the portion manual drain body (43) that contacts the bowl, and the hole in the manual drain body that accommodates the stem of drain valve (41) with o-ring grease.
- Lubricate valve stem (62), adjusting screw threads and tip (3, 7) and the recess of spring rest (10) with a light coat of good quality o-ring grease.
- 3. Lubricate bonnet threads (2, 9) with a small amount of anti-seize compound.
- 4. Assemble the unit as shown on the exploded view.
- 5. Assemble the liquid indicator parts (19 thru 26, 30 thru 37) to reservoir. Apply a 0.9 to 1.8 kg (2 to 4 pound) clamping force to upper and lower sight glass brackets (20, 31). Tighten screws (19, 30).
- 6. Torque Table

Item	Torque in Nm	(Inch-Pounds)
2, 9 (Bonnet)	62 68	(550 600)
16 (Pipe plug)	3,3 5,5	(29 49)
19, 30 (Screw)	1,8 2,3	(16 20)
45, 50 (Nut)	0,8 1,2	(7 10)
53 (Baffle)	1,1 1,4	10 12)

WARNING

These products are intended for use in industrial compressed air systems only. Do not use these products where pressures and temperatures can exceed those listed under Technical Data.

Polycarbonate plastic bowls can be damaged and possibly burst if exposed to such substances as certain solvents, strong alkalies, compressor oils containing ester-based additives or synthetic oils. Fumes of these substances in contact with the polycarbonate bowl, externally or internally, can also result in damage. Clean with warm

Use metal bowl in applications where a plastic bowl might be exposed to substances that are incompatible with polycarbonate. If outlet pressure in excess of the filter/regulator pressure setting could cause downstream equipment to rupture or malfunction, install a pressure relief device downstream of the filter/regulator. The relief pressure and flow capacity of the relief device must satisfy system requirements.

The accuracy of the indication of pressure gauges can change, both during shipment (despite care in packaging) and during the service life. If a pressure gauge is to be used with these products and if inaccurate indications may be hazardous to personnel or property, the gauge should be calibrated before initial

installation and at regular intervals during use. Before using these products with fluids other than air, for non industrial applications, or for life-support systems consult Norgren.

