

Smooth, accurate movement
Long, uninterrupted service life
Low weight
Compact size
Integral magnets for positional feedback



Technical data

Medium:
 Compressed air, filtered, lubricated or non-lubricated
Operation:
 Single acting, angular, magnetic piston
Operating pressure:
 2 to 7 bar
 (Ø 8 mm 3,6 to 7 bar Ø 10 mm 3 to 7 bar)
Operating temperature:
 0°C to +60°C
 * Air supply must be dry enough to avoid ice formation at temperatures below +2°C

Mounting:
 Mounting holes on three faces

Mechanical life:
 ~ 5 million cycles before maintenance may be necessary

Operating frequency:
 180 cycles per minute maximum

Materials

Body: aluminium alloy
 Fingers: carbon steel
 Elastomers: nitrile

Ordering information

To order a gripper with an effective closing grip force of up to 1,4N at 5 bar quote:
M/160306/M/11



Order magnetically operated switches separately

Accessories

Switch M/344

See page

2





Standard models • Effective gripping force • Air consumption


Model	Effective gripping force (N) at 5 bar*		Air consumption (cm ³) at 5 bar**
	Opening	Closing	
M/160305/M/11	0,6	1,0	0,06
M/160306/M/11	1,0	1,4	0,1
M/160307/M/11	2,8	10	0,65
M/160308/M/11	6	18	1,3
M/160309/M/11	10	38	2,4

* Grip point L = 30 mm


** per cycle

Theoretical closing gripping forces


M/160305/M/11




M/160306/M/11




M/160307/M/11




M/160308/M/11



M/160309/M/11



Workpiece




Effective closing gripping forces = Theoretical closing gripping force x 0,85

Switches with LED indication

Model	2-wire solid state	3-wire solid state	Voltage V d.c.	Current max.	Temperature °C	LED	Features	Cable length	Cable type	Straight cable connection	90° elbow cable connection
M/344/EAU/1APV			10 ... 28	20 mA	0° ... +60°	●	-	1 m	PVC	-	●
M/344/EAU/1PV			10 ... 28	20 mA	0° ... +60°	●	-	1 m	PVC	●	-
M/344/EAU/3APV			10 ... 28	20 mA	0° ... +60°	●	-	3 m	PVC	-	●
M/344/EAU/3PV			10 ... 28	20 mA	0° ... +60°	●	-	3 m	PVC	●	-
		M/344/EAN/1APV	4,5 ... 28	50 mA	0° ... +60°	●	NPN	1 m	PVC	-	●
		M/344/EAN/1PV	4,5 ... 28	50 mA	0° ... +60°	●	NPN	1 m	PVC	●	-
		M/344/EAN/3APV	4,5 ... 28	50 mA	0° ... +60°	●	NPN	3 m	PVC	-	●
		M/344/EAN/3PV	4,5 ... 28	50 mA	0° ... +60°	●	NPN	3 m	PVC	●	-



Dimensions



* Port size

	Ø	A	B	C	D	E	F	G	H	I	K
M/160305/M/11	8	12	1,5	2,0	12,5	29	5,5 -0,03	13	24	5,5	2,5
M/160306/M/11	10	14	1,5	2,5	14,5	36	7 -0,03	16	30	6	3
M/160307/M/11	16	24	3	3	17,5	42,5	9 -0,03	18	35	8	3
M/160308/M/11	20	30	3,5	3,5	22	50	12 -0,03	19	39,5	10	4
M/160309/M/11	25	36	4	5	26	58	14 -0,03	21,5	45,5	12	5
	Ø	L	M	O	P	Q	R	S	T	U	V
M/160305/M/11	8	18,5	20	15	Ø 9 +0,05 deep 1	13	9	4,5	-	-	14,5
M/160306/M/11	10	20	23	17	Ø 11 +0,05 deep 1,5	16	10	7,5	10	10	19
M/160307/M/11	16	22,5	34	26	Ø 17 +0,05 deep 1,5	22	14	7,5	12	14	22
M/160308/M/11	20	25	45	35	Ø 21 +0,05 deep 1,5	26	16	8	13	16	24,5
M/160309/M/11	25	28,5	52	40	Ø 26 +0,05 deep 1,5	32	20	9	18	20	28
	Ø	W	X	Y	AA				AB	AC	kg
M/160305/M/11	8	15	17,5	30° -10°	M2,5 x 0,45 deep 4,5 (base); M3 x 0,5 deep 3,5 (side); Ø 3,2 (front)				M3 x 0,5	M2,5 x 0,45	0,02
M/160306/M/11	10	18	20,5	30° -10°	M3 x 0,5 deep 5				M3 x 0,5	M3 x 0,5	0,04
M/160307/M/11	16	24	25	30° -10°	M4 x 0,7 deep 7				M5 x 0,8	M3 x 0,5	0,10
M/160308/M/11	20	30	32,5	30° -10°	M5 x 0,8 deep 8				M5 x 0,8	M4 x 0,7	0,18
M/160309/M/11	25	36	38,5	30° -10°	M6 x 1 deep 10				M5 x 0,8	M5 x 0,8	0,31

Warning

These products are intended for use in industrial compressed air systems only. Do not use these products where pressures and temperatures can exceed those listed under 'Technical Data'.

Before using these products with fluids other than those specified, for non-industrial applications, life-support systems, or other applications not within published specifications, consult NORGREN.

Through misuse, age, or malfunction, components used in fluid power systems can fail in various modes.

The system designer is warned to consider the failure modes of all component parts used in fluid power systems and to provide adequate safeguards to prevent personal injury or damage to equipment in the event of such failure.

System designers must provide a warning to end users in the system instructional manual if protection against a failure mode cannot be adequately provided.

System designers and end users are cautioned to review specific warnings found in instruction sheets packed and shipped with these products.