

- Rotation fully adjustable between two stops
- Intermediate stops possible
- Adjustable hydraulic damping at end stop positions
- Non-contact signal detection via inductive proximity sensors (PNP type) with connector plugs
- Speed control by means of flow regulators

**Rotary Module
Double Acting
270° Rotation**



Technical Data

Medium:

Compressed air, filtered and lubricated

Operating Pressure:

4 - 8 bar

Operating Temperature:

+5°C to +70°C

Operation:

Double acting 270° rotary movement with internal oil damping

Connection:

Electro-pneumatic multi-connector

Theoretical Torque (at 6 bar supply pressure):

24 Nm

Materials

Aluminium outer cover, steel rotary plate.

Ordering Information

To order a Rotary Module with 270° rotation quote:
M/60260.



Basic Dimensions – Rotary Module M/60260

I

