

- Three timing bands allow a range of applications
- Entirely pneumatic - particularly suitable for use in hazardous environments
- Sub-base mounted with bottom ports
- Suitable for panel mounting


**Pneumatic Timer
M5**

Technical Data

Medium:

Compressed air, filtered, lubricated and non-lubricated

Operation:

Pneumatic timer

Mounting:

Through-holes in sub-base, threaded

Port Size:

M5

Operating Pressure:

1,5 - 8 bar

Flow (to CETOP RP50P):

'C' - Conductance $\text{dm}^3/\text{s}/\text{bar}$ 0,006

Timing Ranges:

0,5 - 60 seconds


0,5 - 120 seconds

0,5 - 180 seconds

Operating Temperature:

-20°C* to +60°C

*Consult our Technical Service for use below +2°C


Materials

Plastic body, aluminium sub-base, nitrile rubber seals.

Ordering Information

To order, quote model number M/50901




General Information

Model	Sub-base	Type	Port size	Weight (kg)	Spares kit
M/50901	Bottom ported	Normally closed	M5	0,24	Not available

Warning

These products are intended for use in industrial compressed air systems only. Do not use these products where *pressures* and *temperatures* can exceed those listed under 'Technical Data'. Before using these products with fluids other than those specified, for non-industrial applications, life-support systems, or other applications not within published specifications, consult NORGREN MARTONAIR. Through misuse, age, or malfunction, components used in fluid power systems can fail in various modes. The system designer is warned to consider the failure modes of all component parts used in fluid power systems and to provide adequate safeguards to prevent personal injury or damage to equipment in the event of such failure. **System designers must provide a warning to end users in the system instructional manual if protection against a failure mode cannot be adequately provided.** System designers and end users are cautioned to review specific warnings found in instruction sheets packed and shipped with these products.

Pneumatic Timer



Model Number: M/50901