

- Widely used in delay circuit applications
- Simple, neat, compact design
- Switches can be ganged together



**Pressure Switch
G¹/₈**



Technical Data

Medium:

Compressed air, filtered, lubricated and non-lubricated

Operation:

Pressure switch

Mounting:

Through-holes in switch body

Port Size:

G¹/₈

Operating Pressure:

2 - 10 bar

Minimum Switching Pressure:

50% of supply pressure approximately

Operating Temperature:

-20°C* to +80°C

*Consult our Technical Service for use below +2°C

Materials



Diecast zinc alloy body, nitrile rubber seals

Ordering Information

To order, quote model number M/151.

Alternative Models

N.P.T. ports





M/151

General Information

Model	Port Size	Weight (kg)	Spares kit
M/151	G ¹ / ₈	0,14	QS/151/00

Warning

These products are intended for use in industrial compressed air systems only. Do not use these products where *pressures* and *temperatures* can exceed those listed under 'Technical Data'.



Before using these products with fluids other than those specified, for non-industrial applications, life-support systems, or other applications not within published specifications, consult NORGREN MARTONAIR.

Through misuse, age, or malfunction, components used in fluid power systems can fail in various modes. The system designer is warned to consider the failure modes of all component parts used in fluid power systems and to provide adequate safeguards to prevent personal injury or damage to equipment in the event of such failure.

System designers must provide a warning to end users in the system instructional manual if protection against a failure mode cannot be adequately provided.

System designers and end users are cautioned to review specific warnings found in instruction sheets packed and shipped with these products.

Pressure Switch



Model Number: **M/151**

A tie rod kit is available for gang mounting up to 6 of these switches, reference **QM/20151/25**.