

- > -1 ... 16 bar  
Port size: G1/4 or flange
- > Diagnostic function acc. to DESINA
- > Display of system pressure in bar »programmable«
- > Easy programming of switchpoints
- > Economic solution for industrial applications
- > Switching status indicated by 3-colour-LED-Display
- > Free of lacquer impairing substances
- > Application: not for outdoor use



### Technical features

#### Medium:

Gaseous, aggressive and neutral, not-combustible

#### Pressure range:

-1 ... 1, ...10 or ...16 bar  
(-14.5 ... 14.5, ... 145, ... 232 psi)

#### Switching pressure difference:

Programmable

#### Switching point:

Adjustable between  
0 ... 100% of full scale (FS)  
(smallest adjustable pressure switching difference between switching point and reset point  $\geq 0,5\%$  of full scale (FS))

#### Display:

Green:  
Pressure  $\geq$  SP1 (increasing pressure)  
Pink:  
Pressure  $\leq$  RP (drop pressure)  
Pressure < SP (increasing pressure)  
Red:  
System fault - display

#### Mounting position:

Optional

#### Total accuracy:

$\pm 1,5\%$  of full scale (FS) -  
(linearity, hysteresis, repeatability)

#### Shockproof:

30 g, xyz, DIN EN 60068-2-27

#### Vibrationproof:

10 g, 5 ... 500 Hz, xyz,  
DIN EN 60068-2-6

#### Degree of protection acc. to DIN 40050:

IP65 (< 10 bar), IP67 ( $\geq 10$  bar), with plug mounted)

#### Weight:

0,06 kg (13.23 lbs)

#### Temperature sensitivity:

Zero point:  $\pm 0,4\%$  of final value (FS) pro  $10^\circ$  Kelvin  
Range:  $\pm 0,4\%$  of final value (FS) pro  $10^\circ$  Kelvin

#### Ambient/Media temperature:

Ambient:  
-20 ... +80°C (-4 ... +176°F)  
Media:  
-25 ... + 80°C (-13 ... +176°F)  
Air supply must be dry enough to avoid ice formation at temperature below +2°C (+35°F)

#### Materials:

Housing:  
Aluminium/Stainless steel  
Sensor (fluid-affected parts):  
Silizium/Aluminium

FS = full scale

### Electrical parameters

#### Electrical connection:

M12 x 1

#### Power supply:

UB = 18 ... 32 V d.c.

#### Permissible residual ripple:

10% (within UB)

#### Current consumption:

< 100 mA (without load current)

#### Switching mode:

PNP, potential-bound open collector switching to UB

#### Output signal:

Out 1: switching:  
UB minus 1,5V/Imax. 250 mA  
Out 2: diagnostic/switching  
UB minus 1,5V/250 mA

Surge and short-circuit protection (Out1/Out2)

#### Response time:

< 10 ms

#### Service life:

Min. 50 million switching cycles


#### Switching logic Out 1 & 2:

NO/NC programmable

#### Electromagnetic compatibility:

According to EN 61326-1

### Technical data

| Symbol  | Port size | Switching pressure range (bar) (psi) |                | Over pressure *1 (bar) (psi) |     | Output signal *2) | Model   |
|---|-----------|--------------------------------------|----------------|------------------------------|-----|-------------------|---------|
|  | G1/4      | - 1 ... 1                            | -14.5 ... 14.5 | 6                            | 87  | 2 x PNP           | 0860110 |
|   | G1/4      | 0 ... 10                             | 0 ... 145      | 25                           | 362 | 2 x PNP           | 0860120 |
|   | Flange    | 0 ... 10                             | 0 ... 145      | 25                           | 362 | 2 x PNP           | 0860126 |
|   | G1/4      | 0 ... 16                             | 0 ... 232      | 40                           | 580 | 2 x PNP           | 0860130 |

Connector is not in scope of delivery

\*1) Short-term pressure peaks are not allowed to exceed this limit value during operation. Operative utilization of the limit value is not permitted. The limit value corresponds to the maximum testing pressure

\*2) Mode of OUT2 is programmable: Diagnostic acc. to DESINA / switching, switching logic of OUT1 and /OUT2 is programmable (NO/NC)

**Accessories**

**Pressure port reducing nipple**

**Surge damper**

|                           |                           |
|---------------------------|---------------------------|
| 0574767 (brass)           | 0574773 (brass)           |
| 0550083 (stainless steel) | 0553258 (stainless steel) |


**Connector M12 x 1**

| 4- or 5-pin, 90°                                  | 4-pin, 90°                 | 4-pin, straight                | 4-pin, straight         |
|---|----------------------------|--------------------------------|-------------------------|
|   |                            |                                |                         |
| 0523058<br>(2 m cable, 4-core)                    | 0523056<br>(without cable) | 0523057<br>(2 m cable, 4-core) | 0523055 (without cable) |
| 0523053<br>(5 m cable, 4-core)                    |                            | 0523052<br>(5 m cable, 4-core) |                         |
| 0250081 (5 m cable, 5-core, on PE-requirement *1) |                            |                                |                         |


\*1) Cable with screening

**Electrical connection M12 x 1**

| PIN-No. | Signal                | Cable |
|---------|-----------------------|-------|
| 1       | + UB                  | brown |
| 2       | Out 2 (PNP) or DESINA | white |
| 3       | 0 Volt                | blue  |
| 4       | Out 1 (PNP)           | black |
| 5       | Not used              | grey  |



**Dimensions**




Dimensions in mm  
Projection/First angle




**Pressure port reducing nipple**

Model: 0574767 (brass)  
0550083 (stainless steel)



**Surge damper**

Model: 0574773 (brass)  
0553258 (stainless steel)



**Warning**

These products are intended for use in industrial compressed air systems only. Do not use these products where pressures and temperatures can exceed those listed under »Technical features/data«.

Before using these products with fluids other than those specified, for non-industrial applications, life-support systems or other applications not within published specifications, consult IMI NORGREN.

Through misuse, age, or malfunction, components used in fluid power systems can fail in various modes.

The system designer is warned to consider the failure modes of all component parts used in fluid power systems and to provide adequate safeguards to prevent personal injury or damage to equipment in the event of such failure.

System designers must provide a warning to end users in the system instructional manual if protection against a failure mode cannot be adequately provided.

System designers and end users are cautioned to review specific warnings found in instruction sheets packed and shipped with these products.