

26220, 4/2

Indirect solenoid actuated spool valves





- Port size: G1/8 & G1/4
- Compact design
- Standard manual override with detent
- Common exhaust line

Technical features




| | | | |
|---|---|--|--|
| <p>Medium: Compressed air, filtered lubricated or non lubricated</p> <p>Operation: Solenoid operated, indirectly actuated seat valves</p> <p>Operating pressure: max. 10 bar (145 psi)</p> <p>Nominal size:</p> | <p>4 and 7 mm</p> <p>Port size: G1/8, G1/4</p> <p>Mounting position: Any, but preferably with solenoid vertical</p> <p>Flow direction: Fixed</p> | <p>Ambient/Media temperature: -10 ... +60°C (+14 .. +140°F) Depending on solenoid system Air supply must be dry enough to avoid ice formation at temperatures below +2°C (+35°F). If installed in the open protect all connections against the penetration of moisture!</p> | <p>Material: Housing: Aluminium Pilot flange : Plastic (PBT) Seals: NBR</p> |
|---|---|--|--|

Technical data

| Symbol | Port size | Orifice (mm) | Actuation/return | Operating pressure (bar) | | Flow (l/min) | Switching time (ms) | | Manual override | Current draw (W) | Weight (kg) | Dimension No. | Model *1) |
|---|-----------|--------------|---------------------|--------------------------|------|--------------|---------------------|-----|-----------------|------------------|-------------|---------------|-----------|
| | | | | Min. | Max. | | On | Off | | | | | |
|  | G1/8 | 4 | Solenoid/air spring | 1,5 | 10 | 700 | 20 | 20 | Standard | < 5 | 0,30 | 1 | 2622000 |
| | G1/8 | 4 | Solenoid/air spring | 2 | 8 | 700 | 19 | 62 | Standard | < 2 | 0,30 | 1 | 2622001 |
| | G1/4 | 7 | Solenoid/air spring | 1,5 | 10 | 1400 | 24 | 27 | Standard | < 5 | 0,39 | 1 | 2622200 |
| | G1/4 | 7 | Solenoid/air spring | 2 | 8 | 1400 | 23 | 75 | Standard | < 2 | 0,39 | 1 | 2622201 |
|  | G1/8 | 4 | Solenoid/Solenoid | 1,5 | 10 | 700 | 11 | 12 | Standard | < 5 | 0,40 | 2 | 2622100 |
| | G1/8 | 4 | Solenoid/Solenoid | 2 | 8 | 700 | 13 | 14 | Standard | < 2 | 0,40 | 2 | 2622101 |
| | G1/4 | 7 | Solenoid/Solenoid | 1,5 | 10 | 1400 | 24 | 27 | Standard | < 5 | 0,62 | 2 | 2622300 |
| | G1/4 | 7 | Solenoid/Solenoid | 2 | 8 | 1400 | 24 | 27 | Standard | < 2 | 0,62 | 2 | 2622301 |

*1) When ordering please indicate solenoid, voltage and current type (frequency).

Solenoid actuators

| | Power consumption | | Rated current | | Protection class | Ex-Protection | Temperature Ambient/Media | Electrical connection | Weight | Drawing | Circuit diagram | Model |
|--|-------------------|-----------------|----------------|-----------------|-----------------------|--|---------------------------|---|--------|---------|-----------------|-------|
| | 24 V d.c. (W) | 230 V a.c. (VA) | 24 V d.c. (mA) | 230 V a.c. (mA) | | | | | | | | |
|  | 1,8 | — | 70 | — | IP65 (with connector) | — | -15 ... +50 | Connector DIN EN 175301-803, form B *2) | 0,1 | 11 | 1 | 3050 |
| | 4,8 | 8,5 | 70 | — | IP65 (with connector) | — | -15 ... +50 | Connector DIN EN 175301-803, form B *2) | 0,1 | 11 | 1 | 3052 |
|  | 4,4 | 8,0 | 190 | — | IP65 (with connector) | — | -15 ... +50 | Connector DIN EN 175301-803, form A *2) | 0,1 | 12 | 1 | 3030 |
| | 1,6 | — | 30 | — | IP65 (with connector) | — | -15 ... +50 | Connector DIN EN 175301-803, form A *2) | 0,1 | 12 | 1 | 3036 |
|  | 5,0 | — | 210 | — | IP65 (with connector) | II 2 G Ex mb IIC T4/T5 Gb II 2 G Ex mb IIC T4 Gb II 2 D Ex mb tb T130°C Db | -20 ... +50 | Cable length 3 m | 0,3 | 13 | 15 | 3060 |
| | — | 5 | — | 22 | IP65 (with connector) | II 2 G Ex mb IIC T4 Gb II 2 D Ex mb tb T130°C Db | -20 ... +50 *3) | Cable length 3 m | 0,3 | 13 | 15 | 3061 |
| | 2,7 | — | 115 | — | IP65 (with connector) | II 2 G Ex mb IIC T5 Gb II 2 D Ex mb tb T95°C Db | -20 ... +50 *3) | Cable length 3 m | 0,3 | 13 | 14 | 3062 |
| | — | 2,1 | — | 9 | IP65 (with connector) | II 2 G Ex mb IIC T5 Gb II 2 D Ex mb tb T95°C Db | -20 ... +50 *3) | Cable length 3 m | 0,3 | 13 | 15 | 3063 |



Standard voltages (±10%) 24 V d.c., 230 V a.c., other voltages on request.

*2) Connector is not scope of delivery, see table »Accessories«.

*3) With battery assembly max. +40°C (+104°F).

| Model | Approvals | IECEX | | FM | Datasheet |
|-------|------------------|-------|---|----|-----------|
| 306x | ATEX | — | — | — | en.71.560 |
| | PTB 03 ATEX 2015 | — | — | — | en.71.560 |

Accessories


| Connector DIN EN 175301-803 | Silencer *4) |
|---|---|
|  |  |
| 0570275 (Form A) | M/S1 (G1/8) |
| 0680003 (Form B) | M/S2 (G1/4) |

*4) For indoors use only


Dimensions

Dimensions in mm
Projection/First angle

①



②




① Manual override

| Nr. | A | B | D | E | F | G | H | J | K | L | M | øN | øP | R | øS | T | U | Model *5) |
|-----|-------|------|----|-------|----|------|-----|----|----|------|----|-----|----|---|-----|------|----|-----------|
| 1 | 112,5 | — | 40 | G 1/8 | 28 | 20,5 | 9,5 | 25 | 18 | 20,5 | 20 | 4,5 | 8 | 2 | 4,5 | 30 | 19 | 26220 |
| 1 | 127,5 | — | 55 | G 1/4 | 32 | 28,5 | 12 | 30 | 23 | 38,5 | 24 | 4,5 | — | — | 5,5 | 40,5 | 29 | 26222 |
| 2 | 172 | 54 | 40 | G 1/8 | 28 | 25 | 9,5 | 25 | 18 | 25 | 20 | 4,5 | 8 | 2 | 4,5 | 34,5 | 19 | 26221 |
| 2 | 191 | 56,5 | 55 | G 1/4 | 32 | 26 | 12 | 30 | 23 | 36 | 24 | 4,5 | — | — | 5,5 | 38 | 29 | 26223 |


*5) When ordering please indicate solenoid, voltage and current type (frequency).

Solenoids


⑪



⑫




⑬




① Connector can be indexed by 4x90°

Circuit diagrams


①



⑭




⑮



Silencer
Typ: M/S2, M/S4

Dimensions in mm
Projection/First angle



| B | C | G | Ø D | Weight (g) | Model |
|------|------|-----|------|------------|-------|
| G1/8 | 34 | 6,5 | 12,5 | 1,7 | M/S1 |
| G1/4 | 42,5 | 8 | 15,5 | 3,5 | M/S2 |

Warning

These products are intended for use in industrial compressed air systems only. Do not use these products where pressures and temperatures can exceed those listed under »**Technical features/ data**«.

Before using these products with fluids other than those specified, for non-industrial applications, life-support systems or other applications not within published specifications, consult Norgren Ltd.

Through misuse, age, or malfunction, components used in fluid power systems can fail in various modes.

The system designer is warned to consider the failure modes of all component parts used in fluid power systems and to provide adequate safeguards to prevent personal injury or damage to equipment in the event of such failure.

System designers must provide a warning to end users in the system instructional manual if protection against a failure mode cannot be adequately provided.

System designers and end users are cautioned to review specific warnings found in instruction sheets packed and shipped with these products.