

8499898

6-fold high pressure solenoid valve manifold



- > Port size: DN 8, G3/8
- > High pressure solenoid valve manifold
- > Further customized solutions available upon request

Technical features

Medium:

For compressed natural gas (CNG)

Switching function:

Normally closed

Operation:

Indirectly solenoid actuated

Mounting position:

Optional

Flow direction:

Determined

Port size:

G3/8

Operating pressure:

10 ... 320 bar (10 ... 4641 psi)

Leakage:

Internal Leakage acc. to DIN EN 12266-1 Leakage "C"
External Leakage acc. to DIN EN 12266-1 Leakage "A"

Fluid temperature:

-20° ... +60°C (-4° ... +140°F)

Ambient temperature:

-20° ... +50°C (-4° ... +122°F)

Material:

Body: Brass

Seat seal: Polymer

Internal parts: Brass, Stainless steel, Polymer

Installation of a 40 µm filter in front of the valve is required!

Technical data – standard models

Consisting of:	Port size	Nominal Diameter	Flow kv value *1)	Operating pressure max. Differential pressure		Weight (kg)	Model
		(mm)	(m³/h)	(bar)	(psi)		
- 6 solenoid valves to control a dispenser with two lines (parallel filling of two cars)	G3/8	8	1	10 ... 320	10 ... 4641	17,5	8499898.9841.xxxxx
- 6 non return valves to avoid the inflow from higher pressure levels (e.g. High Bank) to lower pressure levels (e.g. Middle Bank)							

xxxxx Please insert voltage and frequency codes

*1) Cv-value (US) = kv value x 1.2

According to PED 2014/68/EU (97/23/EC) and ATEX 2014/34/EU (94/9/EC)!

Option selector
8590**.*******

Port size	Substitute
3/8	898

Frequency	Substitute
See table frequency codes	xx
Voltage	Substitute
See voltage codes	xxx
Solenoid options	Substitute
Solenoid with 10 m cable ends Protection class according to - II 2 G Ex mb IIC T4 Gb - II 2 D Ex mb tb IIIC T130°C Db	9845
For d.c. with 1/2 - 14 NPT female thread and 460 mm flying leads Protection class acc. to ANSI/NEMA USA: FM approved (File-No. 2Z2A6.AE) Canada: CSA certified (File-No. LR 57643-6) Solenoids in temperature class T3C (160°C) are useable in Ex-areas (see table Ex-areas)	3826
For a.c. with integrated rectifier with 1/2 - 14 NPT female thread and 460 mm flying leads Protection class acc. to ANSI/NEMA USA: FM approved (File-No. 2Z2A6.AE) Canada: CSA certified (File-No. LR 57643-6) Solenoids in temperature class T3C (160°C) are useable in Ex-areas (see table Ex-areas)	3827
Solenoid with terminal box cable gland M20 x 1,5 cable clamp ø 5 ... 8 mm Protection class according to - II 2 G Ex e mb IIC T4/T5 Gb - II 2 D Ex tb IIIC T 130°C Db IP66 Ambient temperature: T4 -40 ... +50°C (-40 ... +122°F) T5 -40 ... +40°C (-40 ... +104°F)	428x
Solenoid with terminal box cable gland M20 x 1,5 (cable clamp ø 10 ... 14 mm) 1/2 ... 1/4 NPT (cable clamp ø 7,5 ... 11,9 mm) Protection class according to - II 2 G Ex d mb IIC T4/T5 Gb - II 2 D Ex tb IIIC T 130°C Ambient temperature: T4 -40 ... +50°C (-40 ... +122°F) T5 -40 ... +40°C (-40 ... +104°F)	468x

Standard solenoid systems

Voltage and Frequency Solenoid 9841					
Code Voltage	Code Frequency	Voltage	Frequency	Power consumption	
				Inrush	Holding
024	00	24 V d.c.	-	10,1 W	10,1 W
230	59	230 V a.c.	50 ... 60 Hz	9,2 VA	9,2 VA

Solenoid systems

ATEX category	Protection class	Solenoid	Standard voltages
II 2G	Ex mb IIC T4 Gb	9841	24 V d.c., 110 V a.c., 230 V a.c.
II 2D	Ex mb tb IIIC T130°C Db with 3 m connection cable		

Ex-areas

Solenoid 382x	Class	Divison	Groups
Gases + fumes	I	1 and 2	A ... D
Dusts	II	1 and 2	E ... G
Fibres + fluffs	III	1 and 2	-

Electrical details for all solenoid systems

Voltage range	±10%
Duty cycle	100% ED
Protection class	EN 60529 IP65

According to DIN VDE 0580 at a solenoid temperature of +20°C. At operating state temperature the input power of a coil decreases by up to ca. 30% due to physical reasons.

Dimensions

Dimensions in mm
Projection/First angle

