


- > **Port size: DN 15, G3/4**
- > **High pressure solenoid valves**
- > **Further customized solutions available upon request**


Technical features
Medium:

For compressed natural gas (CNG)

Switching function:

Normally closed

Operation:

Indirectly solenoid actuated

Mounting position:

Optional, preferably with filter on the bottom side

Flow direction:

Determined

Port size:

G3/4

Operating pressure:

10 ... 250 bar (145 ... 3625 psi)

Leakage:

Internal Leakage acc. to DIN EN

12266-1 Leakage "E"

External Leakage acc. to DIN EN

12266-1 Leakage "A"

Fluid temperature:

-20° ... +60°C (-4° ... +140°F)

Ambient temperature:

-20° ... +50°C (-4° ... +122°F)

Material:

Body: Brass

Seat seal: Polymer

Internal parts: Brass,

Stainless steel, Polymer

Technical data - standard models

Consisting of:	Port size	Nominal Diameter (mm)	Operating pressure (max. Differential pressure) (bar)	Weight (kg)	Model Solenoid in V d.c./a.c.
- 3 solenoid valves to control the filling of the Low-, Middle- and High Bank	G3/4	15	10 ... 250	50	8590230.9845.xxxxx
- 6 solenoid valves to control a dispenser with two lines (parallel filling of two cars)					
- 2 solenoid valves as security valves in front of the dispenser					
- 9 non return valves to avoid the inflow from higher pressure levels (e. g. High Bank) to lower pressure levels (e. g. Middle Bank)					
- 2 additional non return valves for filling a car directly from the compressor via the dispenser (without needing to pre-fill the banks), necessary at highly frequented stations					
- 3 Filtern in 40 µm					

xxxxx Please insert voltage and frequency codes

Acc. to PED 2014/68/EU (97/23/EC) and ATEX 2014/34/EU (94/9/EC)!

Option selector

8590★★★★.★★★★.★★★★

Port size	Substitute	Frequency	Substitute
3/4	230	See table frequency codes	xx
		See Voltage Codes	xxx
		Solenoid options	Substitute
		Solenoid with 10 m cabel ends Protection class according to - II 2 G Ex mb IIC T4 Gb - II 2 D Ex mb tb IIIC T130°C Db	9845
		For d.c. with 1/2 - 14 NPT female thread and 460 mm flying leads Protection class acc. to ANSI/NEMA USA: FM approved (File-No. 2Z2A6.AE) Canada: CSA certified (File-No. LR 57643-6) Solenoids in temperature class T3C (160°C) are useable in Ex- areas (see table Ex-areas)	3826
		For a.c. with integrated rectifier with 1/2 - 14 NPT female thread and 460 mm flying leads Protection class acc. to ANSI/NEMA USA: FM approved (File-No. 2Z2A6.AE) Canada: CSA certified (File-No. LR 57643-6) Solenoids in temperature class T3C (160°C) are useable in Ex- areas (see table Ex-areas)	3827
		Solenoid with terminal box cable gland M20 x 1,5 cable clamp ø 5 ... 8 mm Protection class according to - II 2 G Ex e mb IIC T4/T5 Gb - II 2 D Ex tb IIIC T 130°C Db IP66 Ambient temperature: T4 -40 ... +50°C (+32 ... +122°F) T5 -40 ... +40°C	428x
		Solenoid with terminal box cable gland M20 x 1,5 (cabel clamp ø 10 ... 14 mm) 1/2 ... 1/4 NPT (cabel clamp ø 7,5 ... 11,9 mm) Protection class according to - II 2 G Ex d mb IIC T4/T5 Gb - II 2 D Ex tb IIIC T 130°C Ambient temperature: T4 -40 ... +50°C (+32 ... +122°F) T5 -40 ... +40°C	468x

Standard solenoid systems

Voltage and Frequency Solenoid 9841					
Code	Code	Voltage	Frequency	Power consumption	
Voltage	Frequency			Inrush	Holding
024	00	24 V d.c.	-	10,1 W	10,1 W
230	59	230 V a.c.	50 ... 60 Hz	9,2 VA	9,2 VA

Solenoid systems

ATEX category	Protection class	Solenoid	Standard voltages
II2G	Ex mb IIC T4 Gb	9841	24 V d.c., 110 V a.c., 230 V a.c.
II2D	Ex mb tb IIIC T130°C Db with 3 m connection cable		

Ex-areas

	Class	Division	Groups
Gases + fumes	I	1 and 2	A ... D
Dusts	II	1 and 2	E ... G
Fibres + fluffs	III	1 and 2	-

Electrical details for all solenoid systems

Voltage range	±10%
Duty cycle	100% ED
Protection class	EN 60529 IP65

According to DIN VDE 0580 at a solenoid temperature of +20°C.

At operating state temperature the input power of a coil decreases by up to ca. 30% due to physical reasons.

Dimensions

Dimensions in mm
Projection/First angle

