

# P68F - Olympian Plus plug-in system Soft start/dump valves

- > Port size: 3/4" ... 11/2" (ISO G/PTF)
- Assists machine designers in complying with the European Machineries Directive
- Can help existing machinery to comply with PUWER (Provision and Use of Work Equipment Regulations)

#### Technical features Medium:

Compressed air only **Operating pressure:** 3 bar (43 psi) minimum Solenoid actuated: 10 bar (145 psi) maximum Pilot actuated: 17 bar (246 psi) maximum **Snap pressure:** Full flow when downstream pressure reaches 50 ... 80% of inlet pressure **Charge time:** For 25 litre (845 fluid oz) downstream volume and 6,3 bar (90 psi) inlet pressure 6,4 sec.

minimum 115 sec. maximum

- Controlled increase of downstream pressure on start up
- Solenoid, air pilot or manual operator
- High forward flow capacity
- > High flow dump facility



#### Flow:

147 dm<sup>3</sup>/s (312 scfm) (P1 » P2 = Cv 11,2) (P2 » P3 = Cv >11) Operating pressure: 6,3 bar (91 psi) Δp: 0,5 bar (7 psi) **Port sizes:** 3/4", 1", 11/4" or 11/2" **Air pilot port:** 

G1/4 with ISO G main ports 1/4 PTF with PTF main ports Exhaust port: G1 with ISO G main ports 1" PTF with PTF main ports

#### Standard compliance

(only valid for Air pilot/operator version): (C)|| 2G Ex h IIC T6 Gb || 2D Ex h IIC T85° Db

#### Ambient/Media temperature:

Solenoid actuated: -20° ... +50°C ( -4 ... +149°F) Pilot actuated: -20° ... +80°C ( -4 ... +176°F)

#### Materials:

Body, yoke, top and bottom plate: Aluminium Filter discs: Sintered plastic Internal components: Brass/steel Elastomers: NBR

#### Electrical details for solenoid operators

Voltage tolerance	± 10%
Rating	100% continuous duty
Inlet orifice	1,0 mm
Electrical connection	Industrial Standard, 22 mm
Solenoid coil mounting	Four positions x 90°
Protection class	IP 65 (with sealed plug)

#### Technical data - standard models

Symbol	Port size	Size	Actuation/return	Voltage	Pilot port	Weight (kg)	Тур
	G3/4	_	Solenoid/spring	24 V d.c.	_	2,95	P68F-6GC-PFA *1)
	G1	-	Solenoid/spring	24 V d.c.	-	2,93	P68F-8GC-PFA *1)
	G11/4	Basic	Solenoid/spring	24 V d.c.	_	2,90	P68F-AGC-PFA *1)
	G11/2	_	Solenoid/spring	24 V d.c.	-	2,92	P68F-BGC-PFA *1)
	Without yoke		Solenoid/spring	24 V d.c.	_		P68F-BGC-PFA *1)
	G3/4	-	Air/spring	-	1/4"	2,77	P68F-6GA-NNN
	G1	_	Air/spring	_	1/4	2,75	P68F-8GA-NNN
	G11/4	Basic	Air/spring	_	1/4	2,72	P68F-AGA-NNN
	G11/2	_	Air/spring	_	1/4	2,74	P68F-BGA-NNN
	Without yoke		Air/spring	-	1/4		P68F-NNA-NNN

\*1) To select other solenoid type and coil voltage refer to option selector on page 2






## Voltage codes and spare coils

22 mm coil for connector interface acc. to industrial standard								
	Voltage	Power Inrush/Hold	Model	Code				
	12 V d.c.	2 W	QM/48/12J/21	12J				
	24 V d.c	2 W	QM/48/13J/21	13J				
	110/120 V 50/60 Hz	4/2,5 VA	QM/48/18J/21	18J				
	220/240 V 50/60 Hz	6/5,0 VA	QM/48/19J/21	19J				


#### **Connector plugs**



## **Option selector**




## **Flow characteristics**





## Maximum charge time




#### Accessories







## Dimensions

## Pilot actuated Standard




## With manual lockout







With manual lockout




Solenoid actuated

Standard








# Minimum clearance required to remove unit from yoke
Main ports 3/4", 1", 11/4" or 11/2"
Pilot port 1/4"
Plus 10 mm for ports 11/4" or 11/2"
Exhaust port 1"








## Single yoke with bracket




1 For 11/4" and 11/2" ported yokes add 10 mm

## 3/2 Shut-off valve







1 For 1 1/2" ported yokes add 5 mm

1 Two additional plugged G1/4 ports

## Warning

These products are intended for use in industrial compressed air systems only. Do not use these products where pressures and temperatures can exceed those listed under **»Technical features/data«**.

Before using these products with fluids other than those specified, for non-industrial applications, life-support systems or other applications not within published specifications, consult Norgren.

Through misuse, age, or malfunction, components used in fluid power systems can fail in various modes.

125

Dimensions in mm Projection/First angle

 $\ominus \odot$ 

**1** For 1 1/4" and 1 1/2" ported yokes add 10 mm


05

Double yoke with bracket

#### Silencer

1PTF

23



51

51

138

The system designer is warned to consider the failure modes of all component parts used in fluid power systems and to provide adequate safeguards to prevent personal injury or damage to equipment in the event of such failure.

System designers must provide a warning to end users in the system instructional manual if protection against a failure mode cannot be adequately provided.

System designers and end users are cautioned to review specific warnings found in instruction sheets packed and shipped with these products.

08/23

Our policy is one of continued research and development. We therefore reserve the right to amend, without notice, the specifications given in this document. (2002 - 8097i) © 2015 IMI International s.r.o.

MB008A