

- > Port size: G2
- > Oil-fog lubricators for heavy duty lubrication



### Technical features

**Medium:**

Compressed air only

**Maximum inlet pressure:**

10 bar

**Start point:**

 140 dm<sup>3</sup>/s

**Nominal bowl capacity:**

8 litre

**Ambient/Media temperature:**

-20 ... 80°C (-4 ... 176 °F)

Air supply must be dry enough to avoid ice formation at temperatures below 2°C (+35 °F).

**Materials:**

Bowl: steel


Body: aluminium alloy

Elastomers: CR &amp; NBR

Sight feed dome: transparent

PA

### Technical data, standard models


Symbol	Port size	Flow (dm <sup>3</sup> /s) #	Bowl	Bowl capacity (litre)	Weight (kg)	Model
	G2	675	Steel	8	15,00	10-826-999

# Typical flow with 6,3 bar inlet pressure and 0,5 bar pressure drop.

Model listed in the order table must not be located downstream of frequently cycling directional control valves.

Order the optional bi-directional oil-fog lubricator for use under such conditions.

### Flow characteristics




### Service kit

**Service kit**


10-026-100

## Dimensions

Dimensions in mm  
Projection/First angle



## Warning

These products are intended for use in industrial compressed air systems only. Do not use these products where pressures and temperatures can exceed those listed under

### »Technical features/data«.

Before using these products with fluids other than those specified, for non-industrial applications, life-support systems or other applications not within published specifications, consult IMI NORGREN.

Through misuse, age, or malfunction, components used in fluid power systems can fail in various modes.

The system designer is warned to consider the failure modes of all component parts used in fluid power systems and to provide adequate safeguards to prevent personal injury or damage to equipment in the event of such failure.

System designers must provide a warning to end users in the system instructional manual if protection against a failure mode cannot be adequately provided.

System designers and end users are cautioned to review specific warnings found in instruction sheets packed and shipped with these products.