

R38 Precision regulator (stainless steel)

- > Port size: 1/4 NPT
- Designed for use in corrosive environment
- > Metallic parts meet NACE* Standard MR-01-75
- * National Association of Corrosion Engineers – recognised oil-field recommendation for resistance to sulphide stress cracking common in well-head and other corrosive environments
- Technical features Medium:

Compressed air only **Maximum inlet pressure:** 31 bar (450 psig) Applications include marine environment, oil and gas production, chemical and food processing, medical analysis

 Model for precision regulation and high flow



Outlet pressure range: air only 0,04 ... 2 bar (0,5 ... 29

0,04 ... 2 bar (0,5 ... 29 psig), 0,07 ... 4 bar (1 ... 58 psig), 0,25 ... 7 bar (3,6 ... 102 psig), 0,4 ...10 bar (5,8 ... 145 psig) **Port sizes:** 1/4 NPT 1/4 NPT (gauge), 1/8 NPT (relief)

Standard compliances:

KII 2G Ex h IIC T6 Gb II 2D Ex h IIIC T85° Db Ambient/Media temperature: -40 ... +80°C (-40 ... +176 °F) Air supply must be dry enough to avoid ice formation at temperatures below +2°C (+36 °F)

Materials:

Body, bowl, bonnet & adjusting screw: stainless steel Elastomers: Synthetic rubber

Technical data, standard model, relieving

Symbol	Port size	Outlet pressure (bar)	Flow * (dm³/s)	Weight (kg)	Model
	1/4 NPT	0,04 2	8	1,1	R38-240-RNCA
	1/4 NPT	0,07 4	8	1,1	R38-240-RNFA

 * Typical flow with 7 bar inlet pressure, 1 bar set pressure and 0,05 bar drop from set.

Option selector

MountingSubstituteNoneONeck mounting bracket1Panel nut2DiaphragmSubstituteRelievingRNon relievingN

R38-24★-★N★A


>	Outlet pressure Substit adjustment ranges (bar)*	ute
	0,04 2	С
	0,07 4	F
	0,25 7	к
	0,4 10	М
	* 0	

* Outlet pressure can be adjusted to pressures in excess of, and less than, those specified. Do not use these units to control pressures outside of the specified ranges.





Flow characteristics



Spares kit

Valve assembly and diaphragm						
Description	Model					
2 bar relieving	R38-100R					
4 and 7 bar relieving	R38-101R					
10 bar relieving	R38-102R					
2 bar non-relieving	R38-100NR					
4 and 7 bar non-relieving	R38-101NR					
10 bar non-relieving	R38-102NR					









* Stainless steel items not strictly to NACE standard MR-01-75.


Dimensions

5988-02

Accessories







1 1/4 NPT Gauge port 2 1/8 NPT Relief port


Warning


These products are intended for use in industrial compressed air systems only. Do not use these products where pressures and temperatures can exceed those listed under **»Technical features/data«**.

Before using these products with fluids other than those specified, for non-industrial applications, life-support systems or other applications not within published specifications, consult Norgren.

Through misuse, age, or malfunction, components used in fluid power systems can fail in various modes.

Neck mounting bracket





The system designer is warned to consider the failure modes of all component parts used in fluid power systems and to provide adequate safeguards to prevent personal injury or damage to equipment in the event of such failure.

System designers must provide a warning to end users in the system instructional manual if protection against a failure mode cannot be adequately provided.

System designers and end users are cautioned to review specific warnings found in instruction sheets packed and shipped with these products.

Dimensions in mm Projection/First angle