

Polyurethane Tubing - 85A Durometer

- > Recommended for use with Barb Fittings
- > Highly flexible and resistant to kinks / abrasion
- > NSF61, UL94HB, USPIV compliant material
- > UV stabilized
- > Shipped in 100' coils packed in bags



Technical features

Fluid: Compressed Air, Gases, and Liquids	Temperature Rating: -40°F to +165°F (-40° to 74°C)
Materials: Polyurethane	Vacuum Rating: To 28° Hg (711 mm Hg)
Hardness: 85A Durometer	Diameter Tolerances: ±.005"

Tubing		Max Working Pressure @75F	Miniumum Bend Radius	Part Number	Length
OD	ID				
1/8"	1/16"	135 PSI	3/16"	PW20051100	100'
5/32"	3/32"	115 PSI	3/8"	PW20052100	100'
1/4"	1/8"	145 PSI	1/2"	PW20054100	100'
5/16"	3/16"	110 PSI	5/8"	PW20055100	100'
3/8"	1/4"	90 PSI	3/4"	PW20056100	100'

 Warning: Cancer and reproductive harm — www.p65warnings.ca.gov.