# **Pressure Switches**



Diaphragm actuated For neutral gaseous and liquid fluids Switching pressure range 0.02 ... 30 bar

> Catalog Register A 19, P 19, D 4, T 3

Publication 7500610.06.04.99



# Description

Pressure switch for air, gas, water, hydraulic oil, lubricating oil, light fuel oil. Working viscosity up to 1000 mm<sup>2</sup>/s

Repeatability: ±2%

(bezogen auf Druckregelung)
Switching element: Microswitch

Switching element: Microswitch Protection class:: IP 64

Ambient temperature: -10 bis + 80 °C
Fluid temperature: 0 bis + 80 °C

Max. temperature at

switching element: max. + 80 °C
Mounting position: Optional

Max. vibrations: 10 g (sinusoidal) 1)





Type 8 D

#### **Features**

- Small size
- Preferred for pressure monitoring
- Sealed design permits setting of different switching points during operation without tools
- Approved by shipping authorities



Switching function:
Microswitch SPDT
Terminals: 1 – 3: Contacts close on rising pressure
Terminals 1 – 2: Contacts open on rising pressure

1) Tested in accordance with DIN 89011,5.2., within the frequency range 25 ...100 Hz; within frequency range 2 ... 25 Hz tested with amplitude 1.6 mm.

# Parameters Schaltdruckdifferenz festliegend

| Adjustable range                                      | Switching difference |                |       | Switching cycles per minute | Pressure se<br>materials | Pressure sensor materials |  | <br>weight sions | Dimen-<br>sional<br>drawing | Cat. No. |
|---|----------------------|----------------|-------|-----------------------------|--------------------------|---------------------------|--|------------------|-----------------------------|----------|
| p <sub>vu min</sub> p <sub>vo max</sub><br>(VDI 3283) | lower<br>range       | upper<br>range |       |                             | Housing                  | Seal                      |  |                  |                             |          |
| [bar]   | [bar]                | [bar]          | [bar] |                             |                          |                           |  | [kg]             | No.                         |          |

# Setting of switching point by Allen head screw protected by plastic cover Electrical connection: Cable gland Pg 13.5

| 0.2 12 | 0.9 | 1.4 | 50 | max. 60             | Alumi- | NBR     | I | G 1/4 | 0.4 | 01 | 0820150 |
|--------|-----|-----|----|---------------------|--------|---------|---|-------|-----|----|---------|
| 0.2 12 | 0.9 | 1.4 | 50 | (sudden             | nium   | (Perbu- | Р | -     | 0.4 | 03 | 0820250 |
| 0.5 30 | 1.0 | 2.0 | 50 | pressure<br>changes |        | nan)    | 1 | G 1/4 | 0.4 | 01 | 0820750 |
| 0.5 30 | 1.0 | 2.0 | 50 | permissible)        |        |         | Р | _     | 0.4 | 03 | 0820850 |

#### Electrical connection: interface to DIN 43650

| 0.02 2  | 0.12 | 0.12 | 50 | max. 60             | Alumi- | NBR     | I | G 1/4 | 0.4 | 02 | 0820149 |
|---------|------|------|----|---------------------|--------|---------|---|-------|-----|----|---------|
| 0.10 6  | 0.14 | 0.14 | 50 | (                   | nium   | (Perbu- | I | G 1/4 | 0.4 | 02 | 0820148 |
| 0.20 12 | 0.9  | 1.4  | 50 | pressure<br>changes |        | nan)    | 1 | G 1/4 | 0.4 | 02 | 0820155 |
| 0.50 30 | 1.0  | 2.0  | 50 | permissible)        |        |         | I | G 1/4 | 0.4 | 02 | 0820755 |

# Setting of switching point by scaled rotary button Electrical connection: Cable gland Pg 13.5

| 0.2 12 | 0.9 | 1.4 | 50 | max. 60  |      | NBR             | I | G 1/4 | 0.45 | 04 | 0820160 |
|--------|-----|-----|----|--|------|-----------------|---|-------|------|----|---------|
| 0.5 30 | 1.0 | 2.0 |    | (sudden<br>pressure<br>changes<br>permissible) | nium | (Perbu-<br>nan) | I | G 1/4 | 0.45 | 04 | 0820760 |

#### Electrical connection: Connector, interface to DIN 43650

| 0.2 12<br>0.5 30 | 0.9<br>1.0 | 1.4<br>2 | 50<br>50 | max. 60<br>(sudden<br>pressure<br>changes<br>permissible) | Alumi-<br>nium | NBR<br>(Perbu-<br>nan) | I<br>I      | G 1/4<br>G 1/4 | 0.45<br>0.45 | 05<br>05 | 0820166<br>0820765 |
|------------------|------------|----------|----------|---|----------------|------------------------|-------------|----------------|--------------|----------|--------------------|
|                  |            |          |          |   |                |                        | المستمليا ا | ام م م بر ما   |              |          |                    |

I – Internal threadP – Flange (for manifolding)

Approved by GL German. Lloyd, BV Bureau Veritas, DNV Det Norske Veritas, LR Loyd's Register of Shipping, PRS Polski Rejester Statkow, USSR Register of Shipping

## Other versions available on request

- Lockable design
- With smaller switching pressure difference
   Manifold version with up to 8 units


2 7500610.06.04.99


<sup>1)</sup> Even short pressure peaks must not exceed the maximum allowable pressure (= max. test pressure)

# **Dimensional drawings**


01

02






03




O-ring recess for flanged design




Sealing with O-ring dia. 6.07 x 1.78 Cat. No. **0701250** 

04




05



# **Dimensional drawings**

Lockable design, Cat. No. upon request




## **Accessories**

#### Connectors (black) with light indicator

3-pin + protective conductor Connection acc. to DIN 43650 A Optionally available for DC or AC

-with filament lamp -with glow lamp -with glow lamp -with glow lamp 180 to 240 V, Cat. No. **0585418**180 to 240 V, Cat. No. **0585420** 




#### Pressure switch with pilot lamp.

The pilot lamp shows the switching position of the connected pressure switch.


3-pin connector (black) with grounded conductor, interface to DIN 43650  $\mbox{A}$ 

Cat. No. 0570110




#### Reducer, G 1/2 to G 1/4 external thread

Cat. No. 0574767



# Surge damper G 1/4

Cat. No. 0574773



\*) For contact (4) a special lead (mass pot. or -) is required

7500610.06.04.99

# Switch selection and mounting instructions

The switching points should normally be in about the middle of the adjustable range. Do not exceed electrical ratings.

Electrical connection in accordance with local regulations. For outdoor installation sufficient protection has to be

provided for. Critical conditions are: Aggressiveness of air, high or low temperatures, drastic changes in temperature, solar radiation, penetration of water. For liquid fluids with pressure peaks and/or pulsating pressure, install surge damper upstream to eliminate scattering of switching points and excessive wear.

## Setting of switching points


Version with adjustment by screw with hex. recessed hole:

Loosen check nut, then set lower switching point. The upper switch point is determined by the fixed switching pressure difference.

Versions with adjustment by scaled rotary button: Loosen slot bolt, then set lower switching point. The upper switching point is determined by the fixed switching pressure difference.

Turning the setting device clockwise shifts switching points upwards.

Use pressure gauge for precise setting (a pressure switch – even if provided with a scale – is not a measuring instrument). Switches can be adjusted even during operation. Depending on the design, setting can be arrested by either check nut or slot bolt.



7500610.06.04.99

# Making and/or breaking capacity

#### Change-over switch with silver spring contacts

| Туре    |  | Voltage [V]                |     |      |      |  |  |  |  |  |
|---------|--|----------------------------|-----|------|------|--|--|--|--|--|
| of      | Type of load                                       | 24                         | 60  | 110  | 220  |  |  |  |  |  |
| current |  | Make and break current [A] |     |      |      |  |  |  |  |  |
| AC      | Resistive load                                     | 15                         | 15  | 15   | 15   |  |  |  |  |  |
| AC      | Inductive load, $\cos \phi \approx 0.7$            | 4                          | 2.5 | 1.5  | 0.9  |  |  |  |  |  |
| AC      | Inductive load,<br>spark quenching<br>with RC-link | 6                          | 4   | 2.5  | 1.5  |  |  |  |  |  |
| DC      | Resistive load                                     | 2                          | 0.9 | 0.45 | 0.2  |  |  |  |  |  |
| DC      | Inductive load,<br>L/R ≈ 10 ms                     | 1                          | 0.3 | 0.09 | 0.02 |  |  |  |  |  |
| DC      | Inductive load,<br>spark quenching<br>with diode   | 1.5                        | 0.7 | 0.35 | 0.15 |  |  |  |  |  |

Reference number of switchings: 60/min

Reference temperature + 30 °C (with a reference temperature of + 70 °C, I<sub>max</sub> corresponds to 50% of the tabulated values only).

Contact-life appr. 1 x 106 switching cycles at max. current (at 50% of max. current, contact life is appr. 3 times as

Mechanical life appr. 5 x 10<sup>6</sup> switching cycles.

For non-aggressive atmosphere, which in particular does not contain any sulphur, the following limits are valid:

### Microswitch with standard silver contacts:

**U**<sub>min</sub> appr. 8 ... 12 V, I<sub>min</sub> appr. 10 mA, Maximum values acc. to table above

#### Microswitch with gold-plated contacts: (optionally available):

V<sub>min</sub> and I<sub>min</sub>: No lower limit Recommented upper limit:

V<sub>max</sub> appr. 48 V, I<sub>max</sub> appr. 20 mA;

(for higher values silver spring contacts are completely sufficient).

Creepage and air paths correspond to insulation group B according to VDE Reg. 0110 (except contact clearance of microswitch).

#### Spark quenching (direct current):

1. Diode in parallel to inductive load Make sure polarity is correct when making connections.

Dimensioning of quenching diode (rectifier): Rated voltage of diode V<sub>D</sub> ≥ 1.4 x V<sub>Term.</sub> Rated current of diode I<sub>Rated</sub> ≥ I<sub>Load</sub>


Choose quick switching diode (recovery trr ≤ 200 ns)

2. RC-link in parallel to load (or in parallel to switching contact).

Suited for direct and alternating current.

Ratings:

$$\begin{split} & \text{R} \left[ \Omega \right] \approx \text{0.2 x R}_{\text{Load}} \left[ \Omega \right] \\ & \text{C} \left[ \mu \text{F} \right] \approx \text{I}_{\text{Load}} \left[ \text{A} \right] \end{split}$$



Subject to alteration 7500610.06.04.99