





Tandem Line Tooling

norgren.com/automationsolutions

Engineering
GREAT Solutions



Engineering GREAT solutions

*We deliver **GREAT** solutions for our customers tackling the world's most demanding engineering challenges.*


IMI Precision Engineering is a world leader in motion and fluid control technologies. Wherever precision, speed and engineering reliability are essential, we deliver exceptional solutions which improve the productivity and efficiency of our customers' equipment.

Part of IMI plc, (listed on the London Stock Exchange since 1966), IMI Precision Engineering has \$1,214m in sales generated from a sales and service network in 75 countries, as well as manufacturing capabilities in the USA, Germany, China, UK, Switzerland, Czech Republic, Mexico and Brazil. We support this with our global centers of technical excellence and facilities for CFD design and R&D testing. We employ a dedicated team of field engineers, sector specialists and key account managers – all committed to providing excellent service to our customers.

As a business, we aim to **UNDERSTAND** our customers' challenges. We then **CONNECT** our products, people and expertise in order to **DELIVER** exceptional service and solutions. Together these actions **IMPROVE** the performance of our customers' machinery.

We call this Engineering Great. We deliver it to customers through a world-class portfolio of high performance products, and strong partnerships for problem-solving utilizing our global network of support.

The IMI Precision Engineering Auto In-plant Team creates capacity by designing and manufacturing automation and tooling that optimize production throughput in the press room and other material handling applications.



Contents

Tandem Tooling Catalog

1.800.272.4511


Insidesales@imi-precision.com

www.norgren.com/automationsolutions

1

TANDEM CONCEPTS


FAST FIND GUIDE PAGE 04



2

IDLE STATIONS

FAST FIND GUIDE PAGE 08



3

TOOLING CARTS

FAST FIND GUIDE PAGE 10



4

CARBON FIBER STRUCTURES


FAST FIND GUIDE PAGE 12



5

RECEIVERS AND ADAPTERS

FAST FIND GUIDE PAGE 14



6

ROUND TOOLING


FAST FIND GUIDE PAGE 31



7

VACUUM AND ACCESSORIES

FAST FIND GUIDE PAGE 74



8


DOUBLE BLANK ANALYZER


FAST FIND GUIDE PAGE 96



Tandem Tooling Concepts

Through our 65 years of experience in Die Engineering and Press Room Automation, we provide an integrated tooling design that optimizes and stabilizes panel lift and transfer from Front of Line (FOL) to End of Line (EOL) of your Tandem Press.






The IMI Norgren Applications Engineering Team:


- > Maximizes throughput (strokes per minute, SPM) during loading of blanks and unloading of stamped parts
- > Minimizes the cost of capital by overlaying blanks into the fewest possible panel size families
- > Studies potential interference to prevent crashing, avoid downtime and costly repairs
- > Designs the most efficient equipment design to reduce energy consumption and reduce footprint
- > Provides options for reusing, repairing or recycling tooling to maximize program efficiency

NAS World Tool Concept



Reference number	Quantity	Part number	Description	Page reference
1	1	LAA40091BN	Mini bayonet 1.5" Tube 1 /4" NPT	26
2	1	LAA40092BN	Mini bayonet 1.5" Tube 1 /4" NPT	26
3	8	CVC3	Bellows vacuum cup	88
4	4	LWTC10E15E	Featherweight T- Clamp, 1.5" Tube to 1.0" Tube	69
5	8	TLBB-0	Twist-Lok Venturi	80
6	8	XUMB- 1 -155	1 X 155MM Ultra Arm	63
7	2	Z-10-A-250	Poz-E-Lok 1.0 Boom rod tubing	41
8	2	Z-10-A-425	Poz-E-Lok 1.0 Boom rod tubing	41
9	2	Z-15-A-500	Poz-E-Lok 1.5 Boom rod tubing	44
10	1	Air fittings / Air lines	Not shown	


T-Boom with Master Mounts




Drawing reference	Quantity	Part number	Description	Page reference
1	1	Z-TBM-25-A3	Bayonet mount 2.5" tube	28
2	1	Z-25-A-800	Poz-E-Lok 2.5" boom tubing	47
3	2	ZA-025-010	Poz-E-Lok clamp 2.5" to 1.0"	70
4	6	LWBS10E0225	Featherweight bracket arm, single, M8 bolts	57
5	2	LWTA10E30	1.00" Featherweight Aluminum tube	38
6	4	TPBB-0-1	Threaded post cup mount, 3/8 NPT	82
7	2	LAZ1047	Sensor mount, apple core, 30 mm sensor	
8	2	BI15-G30-ADZ30X2-B1131	Barrel sensor 30 mm	
9	6	LWBC10E25	Featherweight Clamp, 1" tube to ball	68
10	4	LTC10-075	Round Vacuum Cup	90
11	2	RSRK 301-738/6F	Electrical cable	
12	1	PL-215-250-DC	Electrical box mount (not shown)	
13	1	A402DSC	Electrical box (not shown)	
14	1	Air fittings / Air lines	Not shown	

Idle Stations



Idle stations are custom engineered solutions for supporting panels in presses. The ergonomic, removable system incorporates the concept of 'poka-yoke' using template location codes to prevent placement mistakes.





Idle Station
Rotator


Idle Station
Spreader



Idle Station
Panel Tipper

Tooling Carts


We offer tooling carts to protect your investment and provide an efficient and space saving solution to your storage needs.



Standard cart
solution

Tooling Carts


End of arm tooling carts are designed to store up to 96 fingers to maximize storage capacity within a small footprint. Store your tooling safely and allow quick changeover to reduce downtime!




Carbon Fiber Structures


Slow line speeds? Shaking and imprecise part placement are common challenges with steel and aluminum booms, due to their weight and rigidity. And because they can't be repaired, a crash means expensive replacement. Carbon fiber booms, in contrast, offer stability and precision. They are lightweight but high strength so they accommodate higher line speeds, and because they resist shaking, they place parts precisely, every time.

Carbon fiber is also valued in harsh operating environments for temperature stability and chemical resistance. IMI Precision Engineering has advanced carbon fiber technology by developing the capability to mold it into complex shapes, such as T-bars, with a variety of loading characteristics to meet user requirements. They can also repair carbon fiber booms, extending equipment life.





Receivers and Adapters



- > Quick-change tooling mount/ docking device
- > Steel locating pins ensure rotational stability
- > Lightweight and compact tool changer
- > Ease of use reduces downtime
- > Improved ergonomics and safety

Fast Find Guide


RECEIVERS AND ADAPTERS

Easy Load Receiver



16

Easy Load Adapter



18

LRR Receiver



20

LRA Adapter



24

FIELD ADAPTERS

Bayonet Heavy Duty




26

Bayonet Mount



27

Tooling Flange




29


Easy Load Receiver

Coming Fall 2017

Easy Load receiver has been engineered with ease of use in mind. It's one-touch loading mechanism makes installation seamless. Optional air, electrics and mechanical coding are available for customization.



- > Rated for 100 ft-lbs dynamic load
- > Simple and safe with one-touch loading mechanism
- > Uses M8 bolts on industry standard 45 mm pattern
- > Optional 8 mm dowels for precise locating
- > Staging position allows multiple tools to be carried in at one time
- > Safety catch feature to prevent tools from falling
- > Optional check valves allow up to 4 high-flow automatic air connections
- > Optional electrics allow up to 8-pin automatic electrical connections
- > Industry leading heavy duty, 6-point contact gold plated pins and sockets for durability and reliability in even the harshest environments
- > Optional 8-pin mechanical code for error-proofing the entire press




Dimensions in inches (mm) are for reference only

Easy Load Adapter

Coming Fall 2017

Easy Load Adapter is tailored to meet harsh environments. Pick from 13 different tooling options to find what works best in your application. Simply latch the adapter to the receiver and you are ready to go.

Easy storage




*Install where
you need them*



*Configurable with
optional modules*




- > Compatible with Easy load receiver
- > Rated for 100 ft-lbs dynamic load
- > Simple and safe with one-touch loading mechanism
- > Optional tooling mounts include: 1.0", 1.25" and 25 mm, Versa knuckle, 1.5" and 40 mm, either in straight (shown) or 90° connection
- > Easy Swing-in tooling design for fast, easy loading
- > Staging position allows multiple tools to be carried in at one time
- > Safety catch feature to prevent the tool from falling
- > Optional air ports allow up to 4 high-flow automatic air connections
- > Optional electrics allow up to 8-pin automatic electrical connections
- > Industry leading heavy duty, 6-point contact gold plated pins and sockets for durability and reliability in even the harshest environment
- > Optional 8-pin mechanical code for error-proofing an entire press



Dimensions in inches (mm) are for reference only

Rail Receiver with rear exit air and/ or electric LRR2XXXXXXXXX

- > Receiver bolts to transfer feedbar
- > Acts as a docking device for quick changeover of transfer fingers
- > Steel locating pins of receiver adapter slide into sleeved holes of receiver face for maximum rotational stability
- > Finger held in receiver by simple one touch spring loaded latch – no locking handle required



Order information

LRR2XXXXXXXXX

Finger Release Handle Type	Code
Mushroom Type	0
"T" Type	5

Mount Type	Code
Long Keyplate	A
Mount Plate Short	B
Mounting Plate	E
Short Keyplate	K
No Keyplate	N

Electric Connector Type and Location	Code
No Connector	NN
3-Pin Backplate Mount	3B
4-Pin Backplate Mount	4B
5-Pin Backplate Mount	5B

Electric Connector Exit Orientation - Note 1	Code
No Connector	N
Rear Exit Connector	R
RH Side Exit Connector	S
LH Side Exit Connector	L
Under Exit Connector	U

Pneumatic Ports and Location - Note 1	Code
No Pneumatic Ports	NN
Rear Exit Pneumatic 2 Ports (1/4-18)	RY
Side Exit Pneumatic 2 Ports (1/4-18)	SY
Rear Exit Pneumatic 2 Port (1/4-19)	BY
Rear Exit Pneumatic 4 Port (1/4-18)	C4
Under Exit Pneumatic 2 Ports (1/4-18)	UY

Tooling Coding	Code
No coding	N
Clear Mechanical Coding - Note 2	M
Red Mechanical Coding - Note 2	R
Mechanical Coding - Note 2	C


Note 1: The exit location of the electrical connector and pneumatic ports must be the same. They must both exit the rear, the side or the bottom.

Note 2: Mechanical Coding block is installed. The actual code is not configured at the factory.

Technical data

Weight:

1.64 lbs. (744 g)






General Table

Note 1: For 2X 8 mm SHCS

Note 2: For 2X 6 mm SHCS


Note 3: Optional locking handle shipped loose for field installation if required

Note 4: For 8 mm locating pin



Short Mounting Plate (K)





(See next page for additional mounting plate options)



Dimensions in inches (mm) are for reference only











Additional Mounting Plates




Dimensions in inches (mm) are for reference only

Air/ Electric Connector Overview



LRA20 Receiver Adapter universal style LRA20UNXXXXX

- > Compatible with series LRR20 or LRR25 Rail Receiver for quick change of transfer finger
- > Steel locating pins of receiver adapter slide into sleeved holes of receiver face for superior rotational stability
- > Versa-Link tubes or branches with 1.25" outer diameter (O.D.) slide inside and are clamped in place with LCH1175 collar clamp
- > 1.75" inner diameter (I.D.) branch clamps with stud can clamp on O.D. for immediate 90° offset



Order information

LRA20UNXXXXX

Pneumatic Ports	Code
No Ports	N
2 Ports - 1/4" tubing	A
2 Ports - 8 mm tubing (similar to 3/8" tubing)	B
2 Ports - 6 mm tubing	C

Electrical Connections	Code
No Electrical Connection	NNN
3-Pin Electrical Connection	3EN
4-Pin Electrical Connection	4EN

Tool Coding	Code
No Coding	N
Device Net Coding	D
Mechanical Coding	M



Technical data

Weight:


394 g

Pneumatic ports - add 66 g

Electrical connector - add 45 g




Application




Dimensions in inches (mm) are for reference only

Optional pneumatic ports and electrical connections



Note 1: Push-in fitting for corresponding plastic tubing utilized.



Dimensions in inches (mm) are for reference only

Heavy Duty Bayonet, 15 Series
LAA4009XXXXX

> Adapter is used with alternative (non-IMI Norgren) quick connect housing

**Order information****LAA4009XXXXX**

Code Position	Code
Top left	1
Bottom left	2
Bottom right	3
Top right	4
None	N




Air Ports	Code
1/8 NPT	A
1/4 NPT	B
1/8 NPT 6 Port	C
1/4 NPT 3 Port	D
1/4 NPT and 3/8 NPT 6 Port	E
None	N

Electric Connections	Code
3 Pin mini	3
5 Pin micro	5
None	N

Tube Size	Code
1.50"	Blank
40 mm	40
1.50" with locking ring	18

Technical data**Weight:**


1.3 lbs / 583 g

**Coding positions**

Dimensions in inches (mm) are for reference only

Bayonet Mount Z-TBM-15-XX-XX

> Works with alternative (non-IMI Norgren) housing




Order information

Z-TBM-15-XX-XX

Air Port	Code	Key Location	Code
None	A0	Position 1	K1
3 Internal Air Ports	A3	Position 2	K2


Technical data



Dimensions in inches (mm) are for reference only

**Bayonet Mount
Z-TBM-XX-XX-XX-XX**

> Adapter is used with alternative (non-IMI Norgren) quick connect housing


Order information
Z-TBM-XX-XX-XX-XX

Boom Diameter	Code
2.5 in	25
60 mm	60

Air Port	Code
None	A0
3 Port	A3
6 Port	A6



Electrical Options	Code
No Electric Plug	E0

Port Option	Code
MT	Metric
ST	Standard

Technical data
Weight:


A0 Option: 3.75 lbs (1.7 kg)

A6 Option: 4.00 lbs (1.8 kg)



Dimensions in inches (mm) are for reference only

Tooling Flange End Mount TFXE-NP



Order information

TFXE-NP

Diameter	Code
1.50"	1
40 mm	4

Mount	Code
End Mount	E

Pilot	Code
Omit Pilot on Mounting Surface	NP


Technical data

Weight:


2.97 lbs. (1.35 kg)

Material:

Aluminum



Dimensions in inches (mm) are for reference only

**Tooling Flange Saddle Mount
TFXS-NP**

Order information
TFXS-NP

Diameter	Code
1.50"	1
40 mm	4

Mount	Code
Saddle Mount	S


Pilot	Code
Omit Pilot on Mounting Surface	NP

Technical data
Weight:

2.80 lbs. (1.27 kg)


Material:

Aluminum



Dimensions in inches (mm) are for reference only

Round Tooling




- > Spline Rods
- > Aluminum, steel and Featherweight Tubing
- > Clamps
- > Ultra Arms
- > Bracket Arm

Fast Find Guide

SPLINE RODS

Spline Rods



34

TUBING

Featherweight Tooling Tubing



38

Aluminum and Steel Tubing



41

BRACKET ARM

Featherweight Bracket Arm



57

EA Bracket Arm



61


ULTRA ARM

Ultra Mount Bracket Metrc



63

HD Ultra Arm Clamp Bracket



65

Fast Find Guide

TELESCOPING ULTRA ARM

IOT Telescoping Ultra Arm



67

CLAMPS

Featherweight Ball Clamp




68

Featherweight Tooling T-clamps




69

Poz-E-Lok Clamp



70



Receiver Mounts



71

**Spline Rod
TRS25-XXX**

> 25 mm spline rod


**Order information****TRS25-XXX**

Length, mm	Code
300	300
XXX	XXX
900	900

*Lengths available: 300 mm to 900 mm,
in 100 mm increments



Technical data

**24 teeth for 15° incremental adjustability
when used with IMI Norgren NorLok brackets and mounts**



Dimensions in inches (mm) are for reference only

Spline Rod
TRS25-XXX





Material: Aluminum

Dimensions in inches (mm) are for reference only


**Spline Rod
TRS40-XXX**

> 40 mm spline rod

**Order information****TRS40-XXX**



Length, mm	Code
300	300
XXX	XXX
1500	1500

*Lengths available: 300mm to 1500 mm,
in 100 mm increments

Technical data

Dimensions in inches (mm) are for reference only

Spline Rod
TRS40-XXX



Material: Aluminum

Dimensions in inches (mm) are for reference only

**Featherweight Tooling Tubing
LWTA10EXXXX**

> 1.00" diameter aluminum tubing




**Order information:****LWTA10EXXXX**

Length*	Code
100	0100
XXXX	XXXX
3650	3650

*Lengths available: 100 mm to 3650 mm
in 25 mm increments

Application notes

Tubes weight 0.03 lbs/in (589 g/m)



Dimensions in inches (mm) are for reference only

Featherweight Tooling Tubing LWTA15EXXXX

> 1.50" diameter aluminum tubing



Order information:





LWTA15EXXXX

Length*	Code
100	0100
XXXX	XXXX
3650	3650

*Lengths available: 100 mm to 3650 mm
in 25 mm increments

Application notes


Tubes weight 0.05 lbs/in (928 g/m)



Dimensions in inches (mm) are for reference only

**Featherweight Tooling Tubing
LWTS10EXXX**

> 1.00" diameter steel tubing





**Order information:****LWTS10EXXX**

Length*	Code
100	0100
XXX	XXX
3650	3650

*Lengths available: 100 mm to 3650 mm
in 25 mm increments


Application notes

Tubes weight 0.09 lbs/in (1607 g/m)



Dimensions in inches (mm) are for reference only

Aluminum and Steel Tubing
Z-10-X-XXXX



Order information

Z-10-X-XXXX


Diameter	Code
1.00" Boom Rod Tubing	10

Material	Code
Steel	S
Aluminum	A



Length, mm	Code
75	75
XXXX	XXXX
900	900

*Lengths available: 75 mm to 900 mm, in 25 mm increments

Technical data





Dimensions in inches (mm) are for reference only


Aluminum and Steel Tubing
Z-10-X-XXXX

Dimensions in inches (mm) are for reference only

Aluminum and Steel Tubing
Z-10-X-XXXX



Dimensions in inches (mm) are for reference only

Aluminum and Steel Tubing
Z-15-X-XXXX

Order information

Z-15-X-XXXX



Diameter	Code
1.50" Boom Rod Tubing	15

Material	Code
Steel	S
Aluminum	A

Length, mm	Code
100	100
XXXX	XXXX
1200	1200



*Lengths available: 100 mm to
1200 mm in 100 mm increments

Technical data




Dimensions in inches (mm) are for reference only

Aluminum and Steel Tubing
Z-15-X-XXXX




Dimensions in inches (mm) are for reference only

**Aluminum and Steel Tubing
Z-15-X-XXXX**


Dimensions in inches (mm) are for reference only

Aluminum and Steel Tubing
Z-25-X-XXXX



Order information

Z-25-X-XXXX



Diameter	Code
2.50" Boom Rod Tubing	25

Material	Code
Steel	S
Aluminum	A



Length, mm	Code
300	300
XXXX	XXXX
1500	1500

*Lengths available: 300 mm to
1500 mm in 300 mm increments

Technical data





Dimensions in inches (mm) are for reference only

Aluminum and Steel Tubing
Z-25-X-XXXX

Dimensions in inches (mm) are for reference only

Aluminum and Steel Tubing
Z-25-X-XXXX



Dimensions in inches (mm) are for reference only

Aluminum and Steel Tubing

Z-25MM-X-XXX



Order information

Z-25MM-X-XXX



Diameter	Code
25 mm Boom Rod Tubing	25MM

Material	Code
Steel	S
Aluminum	A

Length, mm	Code
75	75
XXX	XXX
900	900

*Lengths available: 75 mm to 900 mm, in 25 mm



Technical data





Aluminum = 6.2 (0.25)
Steel = 2.5 (0.109)

Dimensions in inches (mm) are for reference only

Aluminum and Steel Tubing
Z-25MM-X-XXX




Dimensions in inches (mm) are for reference only

Aluminum and Steel Tubing
Z-25MM-X-XXX

Dimensions in inches (mm) are for reference only

Aluminum and Steel Tubing
Z-40MM-X-XXXX



Order information

Z-40MM-X-XXXX



Diameter	Code
40 mm Boom Rod Tubing	40MM

Material	Code
Steel	S
Aluminum	A



Length, mm	Code
100	100
XXXX	XXXX
1200	1200

*Lengths available: 100 mm to 1200 mm, in 100 mm increments

Technical data





Dimensions in inches (mm) are for reference only

Aluminum and Steel Tubing
Z-40MM-X-XXXX


Dimensions in inches (mm) are for reference only

Aluminum and Steel Tubing
Z-40MM-X-XXXX



Dimensions in inches (mm) are for reference only

Aluminum and Steel Tubing Z-60MM-X-XXXX



Order information

Z-60MM-X-XXXX



Diameter	Code
60 mm Boom Rod Tubing	60MM

Material	Code
Steel	S
Aluminum	A

Length, mm	Code
300	300
XXX	XXX
1500	1500

Lengths available: 300 mm to
1500 mm, in 300 mm increments

Technical data



Dimensions in inches (mm) are for reference only

Featherweight Bracket Arms LWBS10EXXXX

- > 50% weight reduction from steel version
- > Made with aircraft aluminum
- > 1.00" clamp diameter, 1.00" aluminum stem diameter



Order information:

LWBS10EXXXX

↓


Single

Length*	Code
100	0100
XXX	0XXX
800	0800




*Lengths available: 100 mm to 800 mm
in 25 mm increments

Application notes

Load limits of 50 lbs-ft (67.5 Nm) recommended for 1.00" bracket arms.



Dimensions in inches (mm) are for reference only


Featherweight Bracket Arms
LWBS10EXXX

Dimensions in inches (mm) are for reference only


Featherweight Bracket Arms

LWBD10EXXXA

- > Aluminum version
- > 1.00" clamp diameter, 1.00" steel stem diameter




Order information:






*Lengths available: 100 mm to 800 mm
in 25 mm increments

Application notes

Load limits of 50 lbs-ft (67.5Nm) recommended for 1.00" bracket arms.




Dimensions in inches (mm) are for reference only

Featherweight Bracket Arms
LWBS10EXXX

Dimensions in inches (mm) are for reference only

EA Bracket Arm EA-00712-XXX

- > 25 mm clamp to 25 mm aluminum stem
- > Made with aircraft aluminum



Order information


EA-00712- XXX

Length, mm	Code
75	75
XXX	XXX
600	600


*Lengths available: 75 mm to 600 mm, in 25 mm increments

Application notes

Load limits of 50 lbs-ft (67.5 Nm) recommended for 25 mm bracket arms.




Dimensions in inches (mm) are for reference only

EA Bracket Arm
EA-00712-XXX

Dimensions in inches (mm) are for reference only

Ultra Mount Bracket – Metric Hardware XUMB-XX-XXX-X

- > Clamps to tooling arms and extends out to a ball or core clamp
- > Locking rotation adjusts in 30° increments



Order information

XUMB-XX-XXX-X

Bore Diameter


Length	Code
1 in	1
25 mm	25

Length


Length, A	Code
75 mm	75
105 mm	105
125 mm	125
155 mm	155
175 mm	175
205 mm	205

Mount	Code
Core Mount	C
None	Blank

Technical data




Dimensions in inches (mm) are for reference only

Ultra Mount Bracket – Metric Hardware
XUMB-XX-XXX-X

Dimensions in inches (mm) are for reference only

HD Ultra Arm Clamp Bracket
TB1A-XXX-XXX-X



Order information

TB1A-XXX-XXX-X


Bore Diameter	Code
1.50"	15E
40 mm	40M

Length, A	Code
100mm	100
XXX	XXX
600mm	600


Mount	Code
Core Mount	C
None	Blank

*Lengths available: 300 mm to 1500 mm in 300 mm increments

Technical data




Dimensions in inches (mm) are for reference only

Ultra Arm
TB1A-XXX-XXX-X

Dimensions in inches (mm) are for reference only

Featherweight Ball Clamp LWBC10E0025

- > Can be used in applications where ball rotation is not required
- > Can be used with 1.125" ball or 1.125" ball
- > Lighter than IMI Norgren Ultra Arm Series



Order information:


LWBC10E0025



Model Designation

Application notes


Load limits of 50 lbs-ft (67.5 Nm) recommended for 1.00" ball clamp.
Weight 0.35 lbs. (0.16 Kg)



Dimensions in inches (mm) are for reference only

Featherweight Tooling T-Clamps LWTCXXXXXX

> Lightweight clamp to provide a 90° connection between tubes



Order information:



LWTCXXXXXX

Clamp 1 Description	Code	Clamp 2 Description	Code
1.00"	10E	1.00"	10E
1.50"	15E	1.50"	15E
25mm	25M	25mm	25M
40mm	40M	40mm	40M

Application notes

Load limits of 100 ft-lbs [135 Nm] recommended for 1.50" and 40mm clamps

Load limits of 50 ft-lbs [67.5 Nm] recommended for 1.00" and 25mm clamps




Standard parts

CATALOG #	LWTC10E10E	LWTC10E15E	LWTC15E15E	LWTC25M25M	LWTC25M40M	LWTC40M40M
"A"	1.00 (25.4)	1.50 (38.1)	1.50 (38.1)	.984 (25)	1.57 (40)	1.57 (40)
"B"	1.00 (25.4)	1.00 (25.4)	1.50 (38.1)	.984 (25)	.984 (25)	1.57 (40)
"C"	1.40 (35.6)	2.08 (52.8)	2.08 (52.8)	1.40 (35.6)	2.08 (52.8)	2.08 (52.8)
"D"	1.40 (35.6)	1.40 (35.6)	2.08 (52.8)	1.40 (35.6)	1.40 (35.6)	2.08 (52.8)
"E"	1.16 (29.5)	1.50 (38.1)	1.75 (44.5)	1.16 (29.5)	1.50 (38.1)	1.75 (44.45)
"F"	3.36 (85.3)	3.96 (100.6)	4.47 (113.5)	3.36 (85.3)	3.96 (100.6)	4.47 (113.5)
"G"	1.10 (27.9)	1.36 (34.5)	1.36 (34.5)	1.10 (27.9)	1.36 (34.5)	1.36 (34.5)
Weight	0.19 lbs (86 g)	0.36 lbs (163 g)	0.56 lbs (252 g)	0.19 lbs (86 g)	0.34 lbs (152 g)	0.44 lbs (199 g)

Dimensions in inches (mm) are for reference only

**Poz-E-Lok
ZA-XXX-XXX**


- > Toothed clamps provide a locked system which delivers excellent holding strength
- > All clamps are interchangeable with adapters that use the gear tooth interface
- > Toothed gear provides 7.5° of incremental adjustment

**Order information:**

Model		Code	
		ZA	

Clamp 1		Code	
Ø 1.00 in Clamp, Smooth		10	
Ø 1.50 in Clamp, Smooth		15	
Ø 25 mm Clamp, Smooth		25	
Ø 25 mm Clamp, Toothed		25N	
Ø 40 mm Clamp, Smooth		40	
Ø 40 mm Clamp, Toothed		40N	

Clamp 2		Code	
Ø 1.00in Clamp, Smooth		10	
Ø 1.50 in Clamp, Smooth		15	
Ø 25 mm Clamp, Smooth		25	
Ø 25 mm Clamp, Toothed		25N	
Ø 40 mm Clamp, Smooth		40	
Ø 40 mm Clamp, Toothed		40N	


Technical data

ZA-40N-40N	
A	2.40 (61)
B	1.10 (28)
C	1.21 (30.8)
D	2.24 (56.8)
E	2.24 (55.6)
F	1.16 (29.6)
G	1.10 (28)
H	2.40 (61)
I	1.57 (40)
J	1.18 (30)
Weight	0.98 lbs / 445 g


Dimensions in inches (mm) are for reference only

Single Mount, 2.5" Boom to 1.0" Rods TM2A

- > Single 90° tube clamp
- > Made with aircraft aluminum





Order information



Technical data

Weight:
1.77 lbs (0.80 kg)


Material:
Aluminum



Dimensions in inches (mm) are for reference only

**Single Mount, 40 mm Boom to 40 mm Rod
TM4B**

- > Single 90° tube clamp
- > Made with aircraft aluminum

**Order information****TM4B**




Model Designation

Technical data**Weight:**

1.64 lbs. (0.74 kg)

Material:


Aluminum



Dimensions in inches (mm) are for reference only

Double Mount TMXX

- > Double 90° tube clamp
- > Made with aircraft aluminum



Order information

TMXX

Rod Conversion	Code
1.5" to 2.5"	2D
40 mm to 40 mm	4E




Technical data

Weight:

2.36 lbs (1.07 kg)


Material:

Aluminum



Dimensions in inches (mm) are for reference only

Vacuum and Accessories




- > Spring Mounts
- > Venturis
- > Vacuum Cups

Fast Find Guide

SPRING MOUNT

Spring Mount (SMX)



77


VENTURI AND CUP MOUNTS

Single Line Port
Venturi with Twist-
Lok Cup Mount
(TLXX-X)

80

Vacuum Cup Venturi
with Threaded Post
Connection
(TPXB-0-X)


81

Threaded Post
Single Line Venturi
(TPXX-X-X)

82

Auto Release Valves
(ARV)

83

Destacker Quick-
Change Vacuum
Cup Holder
(TLCA-X)

84

BELLOWS VACUUM CUP

CVC10
(1.3" diameter)

85

CVC15
(1.7" diameter)

86

CVC2
(2" diameter)

87

CVC3
(3" diameter)

88

CVC4
(4" diameter)

89

ROUND VACUUM CUP

LTC10



90

Fast Find Guide

OVAL CUPS

OVC15



91

OVC13




92

OVC16



93

LTC31-XXX-XXX



94

OVAL BELLOW VACUUM CUPS

LTC37-XXX-XXX





95

Spring Mount SMX

- > Act as an interface connecting a cup to a venturi/ vacuum source
- > Used primarily in destacking applications
- > Allows for different height stacks to be used with the same system
- > Connects to a vacuum pump, air source, or venturi on one end and either a suction cup or a line to a venturi cup combo on the other end
- > Various options available to give maximum versatility to fit a wide variety of tooling situations



Order Information



Dimensions in inches (mm) are for reference only


**Spring Mount
SMX****Diagram A: Unit Measure**

- > All threads are offered in English (NPT) or Metric (BSPT) units to ensure compatibility with any system
- > 3/8 male pipe fitting located on the bottom of the shaft optimal for suction cup attachment
- > 3/8 female pipe thread located at the top of the shaft allowing for a IMI Norgren venturi or other vacuum source attachment

Note: Unit Measure option affects the shaft's ID thread on Top and the OD thread at the bottom.

Order information**SM X XXXX**

Unit Measure	Code
English	E
Metric	M

**Diagram B: Travel Length and Orientation**



- > Travel provides compensation for the height change in the sheet metal stack.
- > A non-inverted or inverted orientation of the spring mount provides flexibility to align the cup to be mounted on the same plane as the sheet metal.

Options selector**SMX X X XX**

Travel Length	Code	Orientation	Code
2" travel	2	Non-Inverted	N
4" travel	4	Inverted	I

Technical data**Weight:**

1.57 lbs (712 g) - 2.26 lbs (1027 g)

**Dimensions**

Stroke Options	"A" in (mm)	"B" in (mm)
2" travel (non-inverted)	5.05 (128.40)	0.185 (4.7)
2" travel (inverted)	4.87 (123.70)	0.185 (4.7)
4" travel (non-inverted)	7.01 (178.07)	0.185 (4.7)
4" travel (inverted)	6.82 (173.37)	0.185 (4.7)

Dimensions in inches (mm) are for reference only

Spring Mount SMX

Diagram C: Attachment Options

> Various mounting options available to allow the spring mount to be attached to any tooling system

Order information

SMXXX XX or XXXX


Attachment Options	Code
Apple Core	AN
Ball Mount	BN
Gear	GN
None	NN

Attachment Options	Code
Ø1" POZ-E-LOK (Smooth)	G10S
Ø25 mm POZ-E-LOK (Smooth)	G25S
Ø25 mm POZ-E-NOR (Toothed)	G25N
Ø1.5" POZ-E-LOK (Smooth)	G15S
Ø40 mm POZ-E-LOK (Smooth)	G40S
Ø40 mm POZ-E-NOR (Toothed)	G40N

Technical data


Weight:

1.57 lbs (712 g) - 2.26 lbs (1027 g)



Dimensions


Clamp Assembly	"C"	"D"
10S	0.8661 (22)	2.81 (71.38)
15S	1.1024 (28)	3.105 (78.88)
25S	0.8661 (22)	2.81 (71.38)
25N	0.8661 (22)	2.81 (71.38)
40S	1.1024 (28)	3.105 (78.88)
40N	1.1024 (28)	3.105 (78.88)
AN	0 (0)	2.75 (69.85)
BN	0 (0)	2.80 (71.12)
GN	0 (0)	1.94 (49.33)
NN	0 (0)	1.75 (44.45)



Dimensions in inches (mm) are for reference only

**Single Line Port Venturi with Twist-Lok Cup Mount
TLXX-X**



- > Compatible with cups that have the IMI Norgren (formerly "ISI") Vac-Lok adapter
- > Ball is compatible with most tooling mounting arms
- > Optional sensing eliminates the need for a part present switch

**Order information****Technical data****Material:**


Brass, Aluminum, Nitrile, Steel

Weight:

0.50 lbs (0.20 g)




Note 1: Vacuum port compatible with 1/4 NPT, ISO G, ISO R, BSSP, BSPT
(thread sealant is recommended for all tapered fittings)

Application

Dimensions in inches (mm) are for reference only

Vacuum Cup Venturi with Threaded Post Connection TPXB-0-X

- > Venturi cup mount for use with vacuum cups that have 3/8"-18 NPT or 3/8"-19 BSP female threaded mounting connections.
- > 3/4" diameter shaft (tooling mount option "S") or 1-1/8" diameter ball (tooling mount option "B") are compatible with most brands of tooling mounting arms.




Order information:

TPXB-0-X



Tooling Mount	Code
3/4" diameter shaft	S
1-1/8" diameter ball	B

Post Thread Option	Code
3/8 NPT	1
3/8 BSPT/ISO R	2

Technical data





Application



Dimensions in inches (mm) are for reference only

**Threaded Post Single Line Venturi
TPXX-X-X**




> Optional manual override button available for instant vacuum release

**Order information****Technical data****Material:**

Aluminum/Viton

Weight:

0.17 lbs (0.075 kg)

**Application**


Dimensions in inches (mm) are for reference only

Auto Release Venturi ARVX-XXXX-XXX

- > ARVs connect the cups to the tooling while creating vacuum for panel transfer
- > Only one airline is required for vacuum generation
- > Blow off is automatic when air pressure is released
- > For faster tooling set-up and adjustment, a manual override push button releases vacuum
- > Ball and swivel mount options allow mounting the ARV to Ultra Arms (XUMB and IOT) or other clamps




Order information



Technical data


Weight:
0.28 lbs. (129 g)



Dimensions in inches (mm) are for reference only

Destacker Quick-Change Vacuum Cup Holder TLCA-X

- > Quick change mount for vacuum cups with IMI Norgren (formerly "Syron") Vac-Lok adapter
- > Female thread connects directly to pogo-stick lifters in destacker
- > Insert and rotate vacuum cup 1/4 turn to lock in place
- > Combine: Easy 1/4 turn vacuum cup inserting and releasing



Order information


TLCA-X

Code	Mounting options
1	Female 3/8 NPT
2	Female 3/8 BSPT/ISO R
3	Male 1/4 NPT



Technical data

Weight:

0.2 lbs (0.1 g)



Male 1/4 NPT TLCA-3 option



Syron/ISI Vac-Loc square
Cup mount adapter. Order vacuum cup with
mounting adapter option "B".

Dimensions in inches (mm) are for reference only

Bellows Vacuum Cup (1.3" diameter) CVC10



Order information

XCVC10-X

Thread Type	Code
Metric	X
English	Leave Blank

Mount Type	Code
Vac-Lok Adapter	Leave Blank
10M Thread Insert	T
3/8 BSPP Thread Stud	PN

Technical data

Cup material:



Urethane, Durometer 45 Shore A

Insert material:


Brass/Aluminum

Threaded stud material:

Steel



Dimensions in inches (mm) are for reference only

**Bellows Vacuum Cup (1.7" diameter)
CVC15****Order information****XCVC15 -X**

Thread Type	Code
Metric	X
English	Leave Blank

Mount Type	Code
Vac-Lok Adapter	Leave Blank
1/4 BSPP Port Metric Only	P

Technical data**Cup material:**




Urethane, Durometer 45 Shore A

Insert material:

Brass/Aluminum

Weight:

1.12 oz (31.8 g)



Dimensions in inches (mm) are for reference only

Bellows Vacuum Cup (2" diameter) CVC2



Order information

XCVC2-X



Thread Type	Code
Metric	X
English	Leave Blank

Mount Type	Code
Vac-Lok Adapter	Leave Blank
Pipe Mount (3/8 BSPP Port METRIC ONLY)	P
Pipe Mount (3/8 NPT Port ENGLISH ONLY, 3/8 BSPT Port METRIC ONLY)	T


Technical data

Cup material:


Urethane,
Durometer 45 Shore A




Part number
English CVC2
Metric XCVC2
Weight
 3.14 oz (89.0 g)




Part number
English CVC2-T
Metric XCVC2-T
Weight
 2.26 oz (64.1 g)



Part number
Metric XCVC2-1
Weight
 2.26 oz (64.1 g)



Dimensions in inches (mm) are for reference only

**Bellows Vacuum Cup (3" diameter)
CVC3****Order information****XCVC3-X**

Thread Type	Code
Metric	X
English	Leave Blank

Mount Type	Code
Vac-Lok Adapter	Leave Blank
Pipe Mount (3/8 BSPP Port METRIC ONLY)	P
Pipe Mount (3/8 NPT Port ENGLISH ONLY, 3/8 BSPT Port METRIC ONLY)	T

Technical data**Cup material:**Urethane, Durometer
35 Shore A**Insert material:**


Brass/Aluminum

Threaded stud**material:**


Steel

Vac-Lok material:

Aluminum




1.25 (31.8) SQ.

**Part number**

English CVC3
Metric XCVC3

Weight


3.78 oz (107.2 g)

**Part number**

English CVC3-T
Metric XCVC3-T

Weight


3.22 oz (91.3 g)

**Part number**

Metric
XCVC3-P

Weight


3.22 oz (91.3 g)

**Part number**

Metric
XCVC3-PN


Weight

3.54 oz (100.3 g)



Dimensions in inches (mm) are for reference only

Bellows Vacuum Cup (4" diameter) CVC4



Order information

XCVC4-X

Thread Type	Code
Metric	X
English	Leave Blank

Mount Type	Code
Vac-Lok Adapter	Leave Blank
Pipe Mount (3/8 BSPP Port METRIC ONLY)	P
Pipe Mount (3/8 NPT Port ENGLISH ONLY, 3/8 BSPT Port METRIC ONLY)	T

Technical data

Cup material:

Urethane, Durometer 45 Shore A

Insert material:



Brass/Aluminum

Threaded stud material:



Steel

Vac-Lok material:


Aluminum



Part number
English CVC4
Metric XCVC4
Weight
6.64 oz (188.21 g)




Part number
English CVC4-T
Metric XCVC4-T
Weight
6.08 oz (172.4 g)



Part number
Metric XCVC4-P
Weight
6.08 oz (172.4 g)

Part number
Metric XCVC4-35PN
Weight
6.49 oz (184 g)



Dimensions in inches (mm) are for reference only

Flat Round Vacuum Cup LTC10

- > Used on flat surfaces
- > Nitrile rubber has superior abrasion and chemical erosion characteristics
- > Triangle pad design provides higher shear force, grip strength and prevents dimpling of material
- > Aluminum core design improves part stability
- > No silicone content



Order information

Part number	Weight
LTC10-050	45 grams
LTC10-075	76 grams
LTC10-100	99 grams

*Ratings are based on 24 in-Hg and oily surface

LTC10-XXX-X

Size (mm)	Code
050 mm	050
075 mm	075
100 mm	100

Mount Interface	Code
3/8 NPT	None
Square Mount	B

Technical data

Material:



Nitrile Rubber

Color:

Blue

Hardness:

60° Shore $\pm 5^\circ$



Part number	A	B	C	Compression Stroke	Lift Force	Shear Force
LTC10-050	2.0 (50)	1.28 (32.5)	3/8 NPT	0.20 (5.0)	94 N 21 lbs	53 N 12 lbs
LTC10-075	3.0 (75)	1.44 (36.5)	3/8 NPT	0.30 (7.6)	249 N 56 lbs	89 N 20 lbs
LTC10-100	4.0 (100)	1.64 (41.7)	3/8 NPT	0.51 (13.0)	405 N 91 lbs	169 N 38 lbs

Dimensions in inches (mm) are for reference only


Oval Vacuum Cup OVCS15

Order information

XOVCS-15X

Thread Type	Code
Metric	X
English	Leave Blank

Omit this designator to order cup with Vac-Lok mount	Code
M10 Thread Insert	T
3/8 BSPP Thread Stud	PN



Technical data

Cup material:

Urethane, Durometer 35 Shore A

Insert material:



Brass/Aluminum

Threaded stud material:

Steel

Vac-Lok material:

Aluminum





Part number

XOVCS-15T

Weight

1.68 oz (0.048 g)




Part number

XOVCS-15

Weight

1.68 oz (0.048 g)




Part number

XOVCS-15PN

Weight

1.68 oz (0.048 g)




Dimensions in inches (mm) are for reference only

**Oval Vacuum Cup
OVCS13****Order information****XOVCS-13X**

Thread Type	Code
Metric	X
English	Leave Blank

Omit this designator to order cup with Vac-Lok mount	Code
Pipe Mount (3/8 NPT Port ENGLISH or 3/8 BSPT Port METRIC)	T
Pipe Mount (3/8 BSPP Port METRIC Only)	P
Threaded Stud (3/8 BSPP METRIC Only)	PN

**Technical data****Cup material:**



Urethane, Durometer 35 Shore A

Insert material:

Brass/Aluminum

Threaded stud material:



Steel

**Part number**

English OVCS13
Metric XOVCS13

Weight


2.00 oz (56.7 g)

**Part number**

English OVCS13T
Metric XOVCS13T

Weight


1.44 oz (40.8 g)

**Part number**

Metric XOVCS13P

Weight

1.44 oz (40.8 g)

**Part number**

Metric XOVCS13PN

Weight

1.76 oz (49.9 g)

Dimensions in inches (mm) are for reference only

Oval Vacuum Cup OVCS16

Order information

XOVCS-16X

Thread Type	Code
Metric	X
English	Leave Blank

Omit this designator to order cup with Vac-Lok mount	Code
Pipe Mount (3/8 NPT Port English or 3/8 BSPT Port Metric Only)	T
Pipe Mount (3/8 BSPP Port METRIC Only)	P
Threaded Stud (3/8 BSPP METRIC Only)	PN

Technical data

Cup material:

Urethane, Durometer 35 Shore A

Insert material:



Brass/Aluminum

Threaded stud material:

Steel

Vac-Lok material:


Aluminum



Part number

English OVCS16
Metric XOVC16

Weight
2.56 oz (72.6 g)



Part number

English OVCS16T
Metric XOVC16T


Weight
2.00 oz (56.7 g)

Part number

XOVCS16P
Weight
2.00 oz (56.7 g)

Part number


XOVCS16PN
Weight
2.32 oz (65.8 g)



Dimensions in inches (mm) are for reference only

Oval Vacuum Cup LTC31

- > Typically used on aluminum or steel panels
- > Provides maximum surface contact on narrow panels or material handled parts
- > Triangular tread pattern provides superior shear grip force strength on oily or wet surfaces
- > Prevent dimple or damage to panel surface
- > Cup's nitrile rubber material has superior abrasion and chemical erosion characteristics



Order information

LTC31-XXX-XXX-X

Cup outer diameter		Cup height		Mount Style	
	Code		Code		Code
50 mm	050	75 mm	075	3/8 NPT	Leave Blank
65 mm	065	100 mm	100	3/8 Vac-Lok	B
		125 mm	125		

Part Number	Outer diameter	Weight	Mounting
LTC31-050X100	2.0" x 4.0" (50 mm x 100 mm)	45 g	NPT
LTC31-065X125	2.5" x 5.0" (65 mm x 125 mm)	76 g	NPT
LTC31-050X100-B	2.0" x 4.0" (50 mm x 100 mm)	45 g	Vac-Lok
LTC31-065X125-B	2.5" x 5.0" (65 mm x 125 mm)	76 g	Vac-Lok

Technical data

Cup material:

Nitrile rubber

Color:

Blue



Hardness:

60° Shore $\pm 5^\circ$

Part Number	A	B	C	D	Compression Stroke	Minimum radius of curvature (Note 1)	Lifting force	Shear force
LTC31-050X100	2.00" (50 mm)	1.28" (32.5 mm)	3/8 NPT	4.00" (100 mm)	0.20" (5.0 mm)	4.0" (101.6 mm)	56 lbs (249 N)	22 lbs (98 N)
LTC31-065X125	2.50" (65 mm)	1.44" (36.5 mm)	3/8 NPT	5.00" (125 mm)	0.30" (7.6 mm)	7.90" (200.7 mm)	90 lbs (400 N)	41 lbs (180 N)
LTC31-050X100-B	2.00" (50 mm)	1.28" (32.5 mm)	3/8 Vac-Lok	4.00" (100 mm)	0.20" (5.0 mm)	4.0" (101.6 mm)	56 lbs (249 N)	22 lbs (98 N)
LTC31-065X125-B	2.50" (65 mm)	1.44" (36.5 mm)	3/8 Vac-Lok	5.00" (125 mm)	0.30" (7.6 mm)	7.90" (200.7 mm)	90 lbs (400 N)	41 lbs (180 N)

*Ratings are based on 24 in-Hg and oily surface

Note 1: Minimum radius of surface at point of contact where the vacuum cup is placed



Dimensions in inches (mm) are for reference only

Oval Bellow Vacuum Cup LTC37

- > Suitable for sensitive panel surfaces such as aluminum or steel blanks
- > Prevents dimple or damage to panel surface
- > Accommodates variations in panel position and/ or surface contour
- > Less internal volume, therefore requiring less time to draw suction when vacuum is applied
- > Triangular tread pattern provides superior shear force and grip strength on oily or wet surfaces
- > Lip design reduces roll-under effect when the panel hits the cup
- > Cup's nitrile rubber material has superior abrasion and chemical erosion characteristics
- > Silicon-free design provides safe transfer of different panel materials



Order information

LTC37-XXX-XXX-X

Cup outer diameter		Cup height		Mount Style	
	Code		Code		Code
45 mm	045	90 mm	090	3/8 NPT	Leave Blank
65 mm	065	125 mm	125	3/8 Vac-Lok	B

Part number	Outer diameter	Weight	Mounting
LTC37-045X090	1.75" x 3.55" (45 mm x 90 mm)	55 g	NPT
LTC37-065X125	2.5" x 5.0" (65 mm x 125 mm)	87 g	NPT
LTC37-045X090-B	1.75" x 3.55" (45 mm x 90 mm)	55 g	Vac-Lok
LTC37-065X125-B	2.5" x 5.0" (65 mm x 125 mm)	87 g	Vac-Lok

Technical data

Cup material:

Nitrile rubber

Color:


Black

Hardness:

60° Shore ±5°

Part number	A	B	C	D	Compression stroke	Lifting force	Shear force
LTC37-045X090	1.75" (45 mm)	3.55" (90 mm)	1.00" (25 mm)	3/8 NPT	0.39" (9.9 mm)	33 lbs (147 N)	16 lbs (71 N)
LTC37-065X125	2.5" (65 mm)	5.0" (125 mm)	1.38" (35 mm)	3/8 NPT	0.55" (13.9 mm)	80 lbs (356 N)	24 lbs (107 N)
LTC37-045X090-B	1.75" (45 mm)	3.55" (90 mm)	1.00" (25 mm)	3/8 Vac-Lok	0.39" (9.9 mm)	33 lbs (147 N)	16 lbs (71 N)
LTC37-065X125-B	2.5" (65 mm)	5.0" (125 mm)	1.38" (35 mm)	3/8 Vac-Lok	0.55" (13.9 mm)	80 lbs (356 N)	24 lbs (107 N)


*Ratings are based on 24 in-Hg and oily surface



Dimensions in inches (mm) are for reference only

Double Blank Analyzer

Recent trends in vehicle manufacturing found automotive stampers faced with the need to process increasingly thicker blanks while working within smaller size constraints.



*Maximum recommended single sheet thickness

Features and Benefits

- > Greater flexibility with capacity to detect single sheet material thickness range up to 6 mm, compared to 4.6 mm with “legacy” sensors.”
- > Ability to detect both ferrous and non-ferrous material reducing the number of cable runs
- > Greater tolerance of air gaps for ease of setup, increased uptime and reliability
- > Upgraded driver boards that are backwards compatible with old style sensors reducing inventory and enabling potential future system upgrades
- > Greater size to measurement ratio – 42 mm sensors have the same range as “legacy” 54 mm sensors
- > The ability to sense aluminum up to 3.0 mm
- > Up to four independent sensors that can be operated from a single controller for greater flexibility at reading different stations

*Double Blank
Analyzer*





Canada

Rochester Hills, MI, USA

Troy, MI, USA

Saline, MI, USA

USA

Miamisburg, OH, USA

Mississauga, Ontario, CA

Brunswick, OH, USA

Birmingham, AL, USA

Mexico

Queretaro, MX

Worcester, UK

UK

Barcelona, SP

Spain

South America

Sao Paulo, BR

Sales and Service

📍 IMI Precision Engineering sales, manufacturing and technical centers

📍 Value Added Resellers/ Distributors



Global Locations and Partners

IMI Precision Engineering – Auto In-plant Locations

USA

Norgren Automation Solutions, LLC

2871 Bond Street
Rochester Hills, MI 48309 USA

Tel: 1-800-272-4511
Fax: 1-800-626-6092
Email: insidesales@imi-precision.com
Web: norgren.com/automationsolutions

USA

Norgren Automation Solutions, LLC

1325 Woodland Drive
Saline, MI 48176 USA

Tel: 1-734-429-4989
Fax: 1-734-429-7689
Email: insidesales@imi-precision.com
Web: norgren.com/automationsolutions

Mexico

Norgren, S.A.

Av. La Montaña No.120
Parque Industrial Querétaro
Sta. Rosa Jáuregui, Querétaro
C.P. 76220

Tel: +52 442 229 50 00
Email: nas.mexico@imi-precision.com

Brazil

IMI Norgren Brazil

Av. Eng. Alberto de Zagottis 696
04675-085 - São Paulo - SP

Tel: +55 11 5698 4000
Fax: +55 11 5698 4001
Email: vendas@imi-precision.com

China

Norgren Co., Ltd

埃迈诺冠商贸（上海）有限公司.

Tel: +86 21 24161800
sales@imi-precision.com.cn

India

IMI Norgren Herion Pvt. Ltd.

A-62, Sector 63,
Noida- 201301
Uttar Pradesh
India

Tel: +91 (0) 120 4089500
Fax: +91 (0) 120 4089599
Email: india@imi-precision.com

Spain

IMI Norgren S.A.

Colom, 391, 2º - Edificio Tecno
08223 Terrassa

Tel: +34 937489800
Email: spain@imi-precision.com

Thailand

Norgren Co., Ltd

120/34 M. 12 Rachadhewa, Bangplee
Samutprakarn
10540 Thailand

Tel: +66 (0) 2 2750 3598
Fax: +60 (0) 2 750 3855
Email: THSales@imi-precision.com

Value Added Resellers (VARs) and Distributors

Coremo Automation Ltd

Unit 9A – Three Springs Trading Estate
Vincent Road
Worcester
WR5 1BW
U.K.

Tel: +44 (0) 1905 360707
Fax: +44 (0) 1905 360708
Email address: sales@coremo.co.uk

Dyak Systems Inc.

6810 Kitimat Road, Unit 8&9
Mississauga, Ontario L5N 5M2
Canada

Tel: 905-567-4157
Fax: 905-567-4158
Email: salesdesk@dyaksystems.com

Kamco, Inc.

326 Park St.
Troy, MI 48083

Tel: 248-585-7400
Fax: 248-585-7751
Email: sales@kamcocontrols.com
Web: www.kamcosales.com

Mosier Fluid Power

2475 Technical Drive
Miamisburg, OH 45342

Tel: 800-232-0676
Email: sales@mosierohio.com

Motion Industries

1605 Alton Road
Birmingham, AL 35210
Tel: 800-526-9328
Web: www.motionindustries.com


Nicholas Press Sales, Inc.

3077 Nationwide Parkway
Brunswick, OH 44212
Tel: 440-652-6604
Fax: 440-389-8666
Email: sales@nicholaspress.com
Web: www.nicholaspress.com

Taihei Boeki Co., Ltd.

Nikken-Sumisei bldg, 4-15-32
Sakai, Naka-ku, Nagoya, 460-0008
Japan

Tel: +81-(0)52-261-5517
Fax: +81-(0)52-261-2017
Email: nagoya@taiheiboeki.co.jp



Did you know?

You can download Press Room Automation catalogs, case studies and more right at your fingertips!

Check out our **Auto In-plant Uberflip** page at:

<http://onenorgren.uberflip.com/h/c/226804-nas>



*Engineering
GREAT Solutions*

Warning

These products are intended for use in industrial systems only. Do not use these products where pressures and temperatures can exceed those listed under Specifications.

Before using these products with fluids other than those specified, for nonindustrial applications, life-support systems, or other applications not within published specifications, consult Norgren.

Through misuse, age, or malfunction, components used in fluid power systems can fail in various modes. The system designer is warned to consider the failure modes of all component parts used in fluid power systems and to provide adequate safeguards to prevent personal injury or damage to equipment in the event of such failure modes.

System designers must provide a warning to end users in the system instructional manual if protection against a failure mode cannot be adequately provided. System designers and end users are cautioned to review specific warnings found in instruction sheets packed and shipped with these products, or posted on the Norgren website under "Downloads." System designers should also provide for all OSHA requirements including Title 29 CFR 1910.147 Lockout/Tagout.

It should be recognized that warnings are valid for any product, regardless of manufacturer, and are not restricted to products manufactured by Norgren. Norgren's reputation for product quality and performance is well established. We feel we have the additional obligation to provide information or warnings to customers to assist them in applying our products in a reasonable and safe manner.

Proposition 65: These products may contain chemicals known to the state of California to cause cancer, or birth defects, or other reproductive harm.

Warranty

Items sold by Norgren are warranted to be free from defects in materials and workmanship for a period of two years* from the date of invoice, provided said items are used according to Norgren's recommended usages. NORGREN'S LIABILITY IS LIMITED TO THE REPAIR OF, REFUND OF PURCHASE PRICE PAID FOR, OR REPLACEMENT IN KIND OF, AT NORGREN'S SOLE OPTION, ANY ITEMS PROVED DEFECTIVE, PROVIDED THE ALLEGEDLY DEFECTIVE ITEMS ARE RETURNED TO NORGREN PREPAID. THE WARRANTIES EXPRESSED ABOVE ARE IN LIEU OF AND EXCLUSIVE OF ALL OTHER WARRANTIES. THERE ARE NO OTHER WARRANTIES, EXPRESSED OR IMPLIED, EXCEPT AS STATED HEREIN.

THERE ARE NO IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE, WHICH ARE SPECIFICALLY DISCLAIMED. NORGREN'S LIABILITY FOR BREACH OF WARRANTY AS HEREIN STATED IS THE EXCLUSIVE REMEDY, AND IN NO EVENT SHALL NORGREN BE LIABLE OR RESPONSIBLE FOR INCIDENTAL OR CONSEQUENTIAL DAMAGES, EVEN IF THE POSSIBILITY OF SUCH INCIDENTAL OR CONSEQUENTIAL DAMAGES HAS BEEN MADE KNOWN TO NORGREN.

Norgren reserves the right to discontinue manufacture of any product or change product materials, design, or specifications.




For further information, scan this QR code or visit
norgren.com/automationsolutions

1

TANDEM CONCEPTS


EXAMPLES OF INTEGRATED TOOLING FOR TANDEM PRESSES



2

IDLE STATIONS

STAGING AREA FOR PANELS IN BETWEEN DIE STATIONS



3

TOOLING CARTS

SPACE SAVING AND EASY ACCESS SOLUTIONS FOR TOOLING STORAGE



4

CARBON FIBER STRUCTURES

STRONG, LIGHTWEIGHT STRUCTURES FOR HIGH SPEED AND STABLE PANEL TRANSFER



5

RECEIVERS AND ADAPTERS

COUPLING DEVICE FOR QUICK CHANGEOVER



6

ROUND TOOLING


PRE-ENGINEERED MODULAR COMPONENTS FOR TRANSFER TOOLING



7

VACUUM AND ACCESSORIES

SPRING MOUNTS, CUPS, AND VENTURIS FOR MATERIAL HANDLING



8

DOUBLE BLANK ANALYZER

ENSURES TRANSFER OF SINGLE BLANKS THROUGH DIES



Norgren, Buschjost, FAS, Herion and Maxseal are registered trademarks of IMI Precision Engineering companies.

©Norgren Automation Solutions, LLC 2017

Due to our policy of continuous development, IMI Precision Engineering reserve the right to change specifications without prior notice.

15500SP us/02/17

Selected Images used under license from Shutterstock.com

Engineering
GREAT
Solutions

 **IMI NORGREN**

 **IMI BUSCHJOST**

 **IMI FAS**

 **IMI HERION**

 **IMI MAXSEAL**